

RIF-LDM-12-24 DC - Plug-in module



2907057

<https://www.phoenixcontact.com/us/products/2907057>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in module, for mounting on RIF-1, RIF-2, RIF-3, and RIF-4, with freewheeling diode and yellow LED, input voltage: 12 V DC ... 24 V DC $\pm 20\%$, polarity A1-, A2+

Commercial data

Item number	2907057
Packing unit	10 pc
Sales key	C465
Product key	CK6536
Catalog page	Page 316 (C-5-2019)
GTIN	4055626181172
Weight per piece (including packing)	2.894 g
Weight per piece (excluding packing)	2.894 g
Customs tariff number	85363010
Country of origin	CN

RIF-LDM-12-24 DC - Plug-in module



2907057

<https://www.phoenixcontact.com/us/products/2907057>

Technical data

Product properties

Product type	Plug-in module
Product family	RIFLINE complete

Electrical properties

Nominal voltage U_N	12 V AC ... 24 V AC
-----------------------	---------------------

Input data

Input voltage range	12 V DC ... 24 V DC
---------------------	---------------------

Approvals

Corrosive gas test

Identification	ISA-S71.04. G3 Harsh Group
	EN 60068-2-60

RIF-LDM-12-24 DC - Plug-in module



2907057

<https://www.phoenixcontact.com/us/products/2907057>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2907057>



CSA

Approval ID: 76787



UL Recognized

Approval ID: FILE E 113228



EAC

Approval ID: RU C-DE.A*30.B.01082

RIF-LDM-12-24 DC - Plug-in module



2907057

<https://www.phoenixcontact.com/us/products/2907057>

Classifications

ECLASS

ECLASS-11.0	27371692
ECLASS-12.0	27371692
ECLASS-13.0	27371692

ETIM

ETIM 9.0	EC002586
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

RIF-LDM-12-24 DC - Plug-in module



2907057

<https://www.phoenixcontact.com/us/products/2907057>

Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com