

D-PTRV 8 WH 8-1 LGS - End cover

3270244

<https://www.phoenixcontact.com/us/products/3270244>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, depth: 80.8 mm, width: 2.2 mm, height: 100 mm, color: white



Your advantages

- Marked 8 ... 1, can be read horizontally
- Space-saving partition and end cover with isolating function
- Same shape as the PTRV... marshalling panel

Commercial data

| | |
|--------------------------------------|--------------------|
| Item number | 3270244 |
| Packing unit | 10 pc |
| Sales key | BE69 |
| Product key | BE6Z1X |
| Catalog page | Page 53 (C-1-2019) |
| GTIN | 4055626260273 |
| Weight per piece (including packing) | 8.46 g |
| Weight per piece (excluding packing) | 8.4 g |
| Customs tariff number | 85389099 |
| Country of origin | PL |

D-PTRV 8 WH 8-1 LGS - End cover

3270244

<https://www.phoenixcontact.com/us/products/3270244>



Technical data

Product properties

| Product type | End cover |
|--------------|-----------|
|--------------|-----------|

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Material specifications

| | |
|--|-------|
| Color | white |
| Material | PA |
| Flammability rating according to UL 94 | V0 |

Dimensions

| | |
|-----------------|---------|
| Width | 2.2 mm |
| End cover width | 2.2 mm |
| Height | 100 mm |
| Depth | 80.8 mm |

D-PTRV 8 WH 8-1 LGS - End cover

3270244

<https://www.phoenixcontact.com/us/products/3270244>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27141133 |
| ECLASS-12.0 | 27141133 |
| ECLASS-13.0 | 27250301 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000886 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

D-PTRV 8 WH 8-1 LGS - End cover

3270244

<https://www.phoenixcontact.com/us/products/3270244>



Environmental product compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values |
|------------|---|

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com