








Specifications:
规格：
Voltage rating:250V AC/DC
额定电压：250V AC/DC
Current rating:1A AC/DC
额定电流：1A AC/DC
Withstanding voltage:300V AC/minute
耐受电压：300V AC/分钟
Temperature range:-40℃-+105℃
温度范围：-40℃-+105℃
Insulation resistance:≥500MΩ
绝缘电阻：≥500MΩ
Contact resistance:≤20mΩ
接触电阻：≤20mΩ
Material:PA6T UL94V-0
材质：PA6T UL94V-0
Plating Category:1U"Gold
镀层：1U"Gold
Wave soldring temperature:255±5℃，10S
波峰焊温度：255±5℃，10S

X1311 F R - 05 - C43 D24
① ② ③ ④ ⑤ ⑥

1.Series No
2.Category:F-Female
3.Welding Board Angle:R-Stright 90°
4.Row No.Pin No:XX-01~40 Pin
5.Plastic height:C=4.3mm
6.Pin Length:D=2.4mm




PCB LAYOUT

| X1311FR-05-C43D24 | PA6T | Brass | X1311W |
|---|---|---|---|
| PART N0 | Material | Material(Pin) | Suitable XKB Wafer |

| MARK | DESCRIPTION | DATE | REVISED | APPROVED |
|---|---|---|---|---|
| | | | | |
| ΔX | | | | |
| ΔX | | | | |
| ΔX | | | | |

REVISIONS

| UNSPECIFIED TOLERANCES | |
|---|---|
| ANGLAR | ±5° |
| L≤ 4 | ±0.2 |
| 4<L≤ 16 | ±0.3 |
| 16<L≤ 63 | ±0.4 |
| L> 63 | ±0.5 |

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

| | | | |
|---|---|---|---|
| DSND | | SCALE: N/A | MODEL TYPE: 1.27mm BTB Connector |
| DWN | | VIEW: | PART NO.: X1311FR-05-C43D24 |
| CHKD | | UNIT: mm/in | DWG NO.: X-X1311FR-05-C43D24 |
| APPD | | SIZE: A4 | |

| WEIGHT | SHEET | REVISION |
|---|---|---|
| | 1/1 | A0 |