

Specification Sheet

Part Number: 156-01295



Head allows for a 0.2" lateral adjustment on stud during installation.
Quick and easy installation ideal for manufacturing environment.

2-Piece Cable Tie/Oval Stud Mount, 8.0" Long, 50lb Tensile, With Thumb Bar, PA66HIRHS, Black, 2000/box

Article Number 156-01295

Type T50R0SBS6USET

Color Black (BK)

Quantity Per carton

Product Description Oval Shaped Stud Mount's special design allows for a 0.2" (5.5mm) lateral adjustment, allowing for any misalignment of the stud or incorrect position of the tie on the cables. The "soft push" mount allows it to be installed onto a weld stud without the use of any tools.

Short Description 2-Piece Cable Tie/Oval Stud Mount, 8.0" Long, 50lb Tensile, With Thumb Bar, PA66HIRHS, Black, 2000/box

Global Part Name T50R0SBS6USET-PA66/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)	25.0
Minimum Tensile Strength (Metric)	110
Length L (Imperial)	8.0
Length L (Metric)	203.2
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.55
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	4.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.87
Height H (Metric)	21.5
Mounting Hole Diameter D (Metric)	M6 x 1

Stud Diameter (Metric)	M6
Material	Polyamide 6.6 (PA66) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66 PA66HIRHS
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)