REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.01.15	桑甚
A1	N/A		图面升级整理图面	2025.12.20	阿树



Recommended P.C.B Layout(±0.05)



TECHNICAL DATE
PIN(OUTER SLEEVE):BRASS,MACHINED CuZn38Pb2
INSULATOR:PPS UL94V−0 COLOUR:BLACK
CURRENT RATING:3Amps
MATING PINø:0.47/0.64mm
CONTACT RESISTANCE: 10mΩ MAX
DIELECTRIC STRENGTH:1000V RMS
OPERALING TEMPERATURE:−40 ℃ TO +105℃
SOLDERING TEMPERATURE:+255℃

PART NO.:

X5521 ① W ② V ③ −2x07 ④ −C46 ⑤ D46 ⑥ 1220 ⑦

① Series No
② Category:W-Aafaer
③ Welding Board Angle:V-Straight 180°
④ Row No-Pin
⑤ Plastic Height:C=4.6mm
⑥ Pin Length:D=4.6mm
⑦ 1220:Type1220

PART NO.	MATERIAL	MATERIAL(TERMINAL)	FINISH(TERMINAL)	MATES WITH XKB PIN HEADER
X5521WV−2x07−C46D46−1220	PPS 94V−0	BRASS	TIN/GOLD 1u"	X5521F

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	

XKB Connection 星创

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	阿树	VIEW:	MODEL TYPE: 2.54mm BTB Style Connecto
CHECKED		UNIT: mm/in	PART NO.: X5521WV−2x07−C46D46−1220
APPROVED		SIZE: A4	DWG NO.: X−X5521WV−2x07−C46D46−1220

SCALE	PAGE	REVISION
N/A	1/1	A1

www.helloxkb.com www.helloxkb.cn www.xk−dg.cn