

Specification Sheet

Part Number: 512REF

Compact to easily fit in a pocket or on a tool belt.

Dispenser can be reloaded over and over, making it cost-effective to use.

Dispenser edge allows easy removal of label liner.

Dispenser protects labels from dirt and moisture before use, extending the life and quality of the labels.



Rite-On Self-Laminating Label Refill, 0.75" x .5" x 1.875", VL, White, 150/roll

Article Number	590-05121
----------------	-----------

Type	RO512REF
------	----------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton's Rite-On Markers are made from a flexible vinyl film and used to mark wire and cable. The self-laminating labels have a clear tail which seals the legend under clear vinyl, maintaining the quality of the labels. The Rite-On markers are packaged in a reusable dispenser made from high impact plastic which is resistant to oils and grease.
---------------------	--

Short Description	Rite-On Self-Laminating Label Refill, 0.75" x .5" x 1.875", VL, White, 150/roll
-------------------	---

Global Part Name	RO512REF-100B-WH
------------------	------------------

Fixation Method	Pasting / Stick
-----------------	-----------------

Variant	Roller form
---------	-------------

Width W (Imperial)	0.75
--------------------	------

Width W (Metric)	19.05
------------------	-------

Bundle Diameter Min (Imperial)	0.26
--------------------------------	------

Bundle Diameter Min (Metric)	6.68
------------------------------	------

Bundle Diameter Max (Imperial)	0.33
--------------------------------	------

Bundle Diameter Max (Metric)	8.38
------------------------------	------

Height H (Imperial)	0.5
---------------------	-----

Height H (Metric)	12.7
-------------------	------

Outside Diameter Max (Imperial)	0.33
---------------------------------	------

Outside Diameter Min (Metric)	6.68
-------------------------------	------

Outside Diameter Min (Imperial)	0.263
---------------------------------	-------

Outside Diameter Max (Metric)	8.38
-------------------------------	------

Material	Type 100B, Vinyl, white transparent, self-laminating (100B)
Material Shortcut	100B
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	150
Package Quantity (Metric)	150
Customs Number	3919102055

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)