

Data sheet

2486.1 ZB 4/6/K GNYE



Clamping yoke, Screw connection, Mounting type: Can be screwed on, Rated cross-section: 4 mm², Colour: Green-yellow

Business data

| | |
|--|---------------|
| Article number | 2486.1 |
| Article name | ZB 4/6/K GNYE |
| GTIN (EAN) | 4044211052799 |
| Packaging unit | 50 |
| Quantity unit | PC |
| Weight per piece (not including packaging) | 3.78 g |
| Weight per piece (including packaging) | 3.79 g |
| Unit of weight | G |
| Customs number | 85369010 |
| Country of origin | DE |
| Prio-Article | 2486.1 |
| Product description | Clamping yoke |

Technical data

Dimensions

| | |
|--------|--------|
| Length | 12 mm |
| Width | 5.5 mm |
| Height | 15 mm |

Ratings

| | |
|---------------------|-------------------|
| Rated cross-section | 4 mm ² |
|---------------------|-------------------|

Connection data

| | |
|---|---------------------|
| Connection principle | Screw connection |
| Wire cross-section single-core (rigid) / stranded, min. | 0.5 mm ² |
| Wire cross-section single core (rigid)/stranded, max. | 4 mm ² |
| Wire cross-section stranded, min. | 0.5 mm ² |
| Wire cross-section stranded, max. | 4 mm ² |
| Stripping length | 12 mm |
| Screw head | Slotted |
| Screw threading | M 3 |
| Tightening torque, min. | 0.5 Nm |
| Tightening torque, max. | 1 Nm |

Materials

| | |
|---------------------------|-----------------------------------|
| Material | Steel |
| Surface | Galvanized, thick-film passivated |
| Insulation housing | Polyamide 6.6 |
| Flammability class UL 94 | V-2 |
| Working temperature, min. | -40 °C |
| Working temperature, max. | 105 °C |
| Screws | Steel |
| Surface screw | Galvanized, thick-film passivated |


Further technical data

| | |
|---------------|-----------|
| Mounting type | Screwable |
|---------------|-----------|

Environmental Product Compliance

| | |
|--------------------------------|----|
| REACH Candidate Substance Note | No |
|--------------------------------|----|

Media



Accessories

Cap

Cap, Colour: Green-yellow

| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>2491.1</u> | K 4/6 GNYE | 4044211052904 | 50 |

##INVERSE##CONTA-CONNECT

Cap, Colour: Green-yellow

| Article number | Article name | GTIN (EAN) | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>2491.1</u> | K 4/6 GNYE | 4044211052904 | 50 |