


Specification Sheet

Part Number: MB4A10A2C2



For use with HellermannTyton T18 - T50 cable ties to provide stability when securing bundles.
4-way opening allows cable ties to be installed parallel or perpendicular to bundles.

The rubber-based adhesive is an economical choice ideal for indoor applications, with a static load weight of 1.1 lb.

Two predrilled holes extend mounting options and solutions.

Extended adhesive liner is easy to remove quickly.

Acrylic Adhesive Cable Tie Mount, 1.12 x 1.12", Use With T18-T50 Cable Tie, PA66, White, 100/pkg

Article Number	151-28420
Type	MB4A
Color	White (WH)
Quantity Per	bag
Product Description	MB4A adhesive mounts are for use with HellermannTyton T18 - T50 Series cable ties to provide stability when securing bundles. The rubber adhesive-backed mounts can be used to secure a bundle and have two predrilled holes to extend mounting options.
Short Description	Acrylic Adhesive Cable Tie Mount, 1.12 x 1.12", Use With T18-T50 Cable Tie, PA66, White, 100/pkg

Global Part Name MB4A-PA66-WH

Length L (Imperial) 1.12

Length L (Metric) 28.5

Fixation Method Adhesive

Width W (Imperial) 1.12

Width W (Metric) 28.5

Cable Ties T18 - T50

Height H (Imperial) .23

Height H (Metric) 5.8

Cable Tie Width Max (Imperial) 0.18

Cable Tie Width Max (Metric) 4.6

Mounting Hole Diameter D (Imperial) 0.18

Mounting Hole Diameter D (Metric) 4.6 mm

Mounting Hole Centers (Imperial) 0.8

Material Polyamide 6.6 (PA66)

Material Shortcut	PA66
Adhesive	Acrylate with base of acrylic foam
Flammability	UL 94 V-2 (excluding adhesive)
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	-31°F to +158°F (-35 °C to +70 °C)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

