REV.	DESCRIPTION	ECN NO.	NAME	DATE





剖面A－A



剖面B－B



RECOMMENDED PCB LAYOUT
PCB TOLERANCE:±0.05







SPECIFICATION:
1.MATERIAL:
HOUSING: LCP UL 94V-0
COLOR:BLACK
CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm
PEG:C2680R-H,T=0.50mm
2.FINISH:
CONTACT:1u"/3u"/5u"/15u" GOLDPLATING ON CONTACT AREA
100u"TIN PLATING ON SOLDERTAILS
30u"NICKEL UNDERPLATING OVER ALL
PEG: 100u" TIN PLATING ON SOLDERTAILS
30u"NICKEL UNDERPLATING OVER ALL







	环保要求	产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

GENERAL TOLERANCE

DIM.	TOL.
.X	±0.30
.XX	±0.20
.XXX	±0.05
GENERAL ANGLE:	
.X°	±3°
.XX°	±2°
.XXX°	±0.5°

DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD

BXCONN®

TITLE: SATA 7+15P 母座 DIP 180° 双排双鱼叉 加长型针2.7

DWG. NO.: SATA-22M-19HM01-P2 | CHECKED: MAX

PART NO.: SATA-22M-19HM01-P2 | DRAWN: ELLA

UNIT:	SCALE:	SHEET:	DWG. SIZE:	LAYER:	APPROVED: WILL
mm	none	1 of 1	A4	bxconn	