REV.	DESCRIPTION	ECN NO.	NAME	DATE







RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE:±0.05





SPECIFICATION:
1.MATERIAL:
HOUSING:LCP UL 94V-0
COLOR:BLACK
CONTACT:PHOSPHOR BRONZE C5191R-H,T=0.25mm
PEG:BRASS C2680R-H,T=0.30mm
2.FINISH:
CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA
100u" TIN PLATING ON SOLDERTAILS
30u" NICKEL UNDERPLATING OVER ALL
PEG:100u" TIN PLATING ON SOLDERTAILS
30u" NICKEL UNDERPLATING OVER ALL





	环保要求	产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

GENERAL TOLERANCE					
DIM.	TOL.				
.X	±0.30				
.XX	±0.20				
.XXX	±0.05				
GENERAL	ANGLE:				
.X°	±3°				
.XX°	±2°				
.XXX°	±0.5°				

DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD

BXCONN®

TITLE: SATA 7+15P 母座 SMT H:6.74 板上型

DWG. NO.: SATA-22M-20HM01-P2 | CHECKED: MAX

PART NO.: SATA-22M-20HM01-P2 | DRAWN: ELLA

UNIT:	SCALE:	SHEET:	DWG. SIZE:	LAYER:	APPROVED:
mm	none	1 of 1	A4	bxconn	WILL