





Notes:
Rated current:3.0A
Withstand Voltage:500V AC/DC
Contact Resistance:20mΩ Max
Insulation Resistance:1000MΩ Min
Operating Temperature:-40℃ TO +105℃
Contact Material:Brass
Plating:G/F
Insulator Material: PA6T UL94V-0 BK



RECOMMENDED PCB LAYOUT (TOP VIEW)
TOLERANCES:±0.05

NO.	DATE	DESCRIPTION	APPROVAL
1	24-04-18	初次发行	Jack
2			
3			
4			
5			

DRAWING: MAO ZI HAO
CHECKED: YAO HUI SONG
APPROVAL: HAN XIAO QIU

GENERAL TOLERANCE
.X: ±0.30 .X°: ±2°
.XX: ±0.20 .XX°: ±1°
.XXX: ±0.10 .XXX°: ±0.5°

UNIT: MM
PROJECTION
SCALE: N/A
SHEET: 1/1

东莞市文章济美电子有限公司

DESCRIPTION: FH2.54*8.5 1*NP PC3.0 180°Y型端
PART NO: 5001-050428-B
REC:1.0
SERIES :
ROHS