| REV. | ZONE | DESCRIPTION | DESIGN | DATE |
|---|---|---|---|---|
| B | | NEW | | |

Pb Process Capable

RoHS Compliant



















NOTES:
1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V_0,COLOR:BLACK.
CONTACT: COPPER ALLOYS.
2.PLATING:
UNDERPLATE: NICKEL.
CONTACT AREA: TIN OVER NICKEL.
3.MULTIMEDIA CARD COMPATIBLE

| PIN NO. | DIM. A | DIM. B | DIM. C |
|---|---|---|---|
| 04 | 6.40 | 1.50 | 2.57 |
| 05 | 6.90 | 2.00 | 3.07 |
| 06 | 7.40 | 2.50 | 3.57 |
| 07 | 7.90 | 3.00 | 4.07 |
| 08 | 8.40 | 3.50 | 4.57 |
| 09 | 8.90 | 4.00 | 5.07 |
| 10 | 9.40 | 4.50 | 5.57 |
| 11 | 9.90 | 5.00 | 6.07 |
| 12 | 10.40 | 5.50 | 6.57 |
| 13 | 10.90 | 6.00 | 7.07 |
| 14 | 11.40 | 6.50 | 7.57 |
| 15 | 11.90 | 7.00 | 8.07 |
| 16 | 12.40 | 7.50 | 8.57 |
| 17 | 12.90 | 8.00 | 9.07 |
| 18 | 13.40 | 8.50 | 9.57 |
| 19 | 13.90 | 9.00 | 10.07 |
| 20 | 14.40 | 9.50 | 10.57 |
| 21 | 14.90 | 10.00 | 11.07 |
| 22 | 15.40 | 10.50 | 11.57 |
| 23 | 15.90 | 11.00 | 12.07 |
| 24 | 16.40 | 11.50 | 12.57 |
| 25 | 16.90 | 12.00 | 13.07 |
| 26 | 17.40 | 12.50 | 13.57 |
| 27 | 17.90 | 13.00 | 14.07 |

| PIN NO. | DIM. A | DIM. B | DIM. C |
|---|---|---|---|
| 28 | 18.40 | 13.50 | 14.57 |
| 29 | 18.90 | 14.00 | 15.07 |
| 30 | 19.40 | 14.50 | 15.57 |
| 31 | 19.90 | 15.00 | 16.07 |
| 32 | 20.40 | 15.50 | 16.57 |
| 33 | 20.90 | 16.00 | 17.07 |
| 34 | 21.40 | 16.50 | 17.57 |
| 35 | 21.90 | 17.00 | 18.07 |
| 36 | 22.40 | 17.50 | 18.57 |
| 37 | 22.90 | 18.00 | 19.07 |
| 38 | 23.40 | 18.50 | 19.57 |
| 39 | 23.90 | 19.00 | 20.07 |
| 40 | 24.40 | 19.50 | 20.57 |
| 41 | 24.90 | 20.00 | 21.07 |
| 42 | 25.40 | 20.50 | 21.57 |
| 43 | 25.90 | 21.00 | 22.07 |
| 44 | 26.40 | 21.50 | 22.57 |
| 45 | 26.90 | 22.00 | 23.07 |
| 46 | 27.40 | 22.50 | 23.57 |
| 47 | 27.90 | 23.00 | 24.07 |
| 48 | 28.40 | 23.50 | 24.57 |
| 49 | 28.90 | 24.00 | 25.07 |
| 50 | 29.40 | 24.50 | 25.57 |
| 51 | 29.90 | 25.00 | 26.07 |
| 52 | 30.40 | 25.50 | 26.57 |
| 53 | 30.90 | 26.00 | 27.07 |
| 54 | 31.40 | 26.50 | 27.57 |
| 55 | 31.90 | 27.00 | 28.07 |
| 56 | 32.40 | 27.50 | 28.57 |
| 57 | 32.90 | 28.00 | 29.07 |
| 58 | 33.40 | 28.50 | 29.57 |
| 59 | 33.90 | 29.00 | 30.07 |
| 60 | 34.40 | 29.50 | 30.57 |

| | | |
|---|---|---|
| X. ±0.50 | X.° ± 2° | UNITS mm |
| .X ±0.30 | .X° ± 1° | |
| .XX ±0.10 | .XX° ± 0.5° | MAT'L |
| .XXX ±0.05 | | |

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司

TITLE: FPC 0.5PH H2.0前掀28P

FPC-28P-0.5PH2.0H-30277

DWG NO.:

CHKD:

DR:

| SCALE | SHEET | REV. |
|---|---|---|
| 1/1 | 1/1 | A1 |