REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		











PIN NO.	DIM. A	DIM. B	DIM. C
04	5.50	1.50	2.57
05	6.00	2.00	3.07
06	6.50	2.50	3.57
07	7.00	3.00	4.07
08	7.50	3.50	4.57
09	8.00	4.00	5.07
10	8.50	4.50	5.57
11	9.00	5.00	6.07
12	9.50	5.50	6.57
13	10.00	6.00	7.07
14	10.50	6.50	7.57
15	11.00	7.00	8.07
16	11.50	7.50	8.57
17	12.00	8.00	9.07
18	12.50	8.50	9.57
19	13.00	9.00	10.07
20	13.50	9.50	10.57
21	14.00	10.00	11.07
22	14.50	10.50	11.57
23	15.00	11.00	12.07
24	15.50	11.50	12.57
25	16.00	12.00	13.07
26	16.50	12.50	13.57
27	17.00	13.00	14.07

PIN NO.	DIM. A	DIM. B	DIM. C
28	17.50	13.50	14.57
29	18.00	14.00	15.07
30	18.50	14.50	15.57
31	19.00	15.00	16.07
32	19.50	15.50	16.57
33	20.00	16.00	17.07
34	20.50	16.50	17.57
35	21.00	17.00	18.07
36	21.50	17.50	18.57
37	22.00	18.00	19.07
38	22.50	18.50	19.57
39	23.00	19.00	20.07
40	23.50	19.50	20.57
41	24.00	20.00	21.07
42	24.50	20.50	21.57
43	25.00	21.00	22.07
44	25.50	21.50	22.57
45	26.00	22.00	23.07
46	26.50	22.50	23.57
47	27.00	23.00	24.07
48	27.50	23.50	24.57
49	28.00	24.00	25.07
50	28.50	24.50	25.57
51	29.00	25.00	26.07
52	29.50	25.50	26.57
53	30.00	26.00	27.07
54	30.50	26.50	27.57
55	31.00	27.00	28.07
56	31.50	27.50	28.57
57	32.00	28.00	29.07
58	32.50	28.50	29.57
59	33.00	29.00	30.07
60	33.50	29.50	30.57

NOTES:
1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V_0,COLOR:BLACK.
CONTACT: COPPER ALLOYS.
2.PLATING:
UNDERPLATE: 50u" NICKEL.
CONTACT AREA: 1u"GOLD OVER 50u"NICKEL.
3.MULTIMEDIA CARD COMPATIBLE

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°		
.XX ±0.10	.XX° ± 0.5°	MAT'L	TITLE: FPC 0.5PH H2.0后掀50P
.XXX ± 0.05			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	FPC-50P-0.5PH2.0H-30252 / DWG NO.:
		Q'TY	CHKD: / DR:

SCALE	SHEET	REV.
1/1	1/1	A1