| REV. | ZONE | DESCRIPTION | DESIGN | DATE |
|---|---|---|---|---|
| B | | NEW | | |
















| PIN NO. | DIM. A | DIM. B | DIM. C |
|---|---|---|---|
| 04 | 5.50 | 1.50 | 2.57 |
| 05 | 6.00 | 2.00 | 3.07 |
| 06 | 6.50 | 2.50 | 3.57 |
| 07 | 7.00 | 3.00 | 4.07 |
| 08 | 7.50 | 3.50 | 4.57 |
| 09 | 8.00 | 4.00 | 5.07 |
| 10 | 8.50 | 4.50 | 5.57 |
| 11 | 9.00 | 5.00 | 6.07 |
| 12 | 9.50 | 5.50 | 6.57 |
| 13 | 10.00 | 6.00 | 7.07 |
| 14 | 10.50 | 6.50 | 7.57 |
| 15 | 11.00 | 7.00 | 8.07 |
| 16 | 11.50 | 7.50 | 8.57 |
| 17 | 12.00 | 8.00 | 9.07 |
| 18 | 12.50 | 8.50 | 9.57 |
| 19 | 13.00 | 9.00 | 10.07 |
| 20 | 13.50 | 9.50 | 10.57 |
| 21 | 14.00 | 10.00 | 11.07 |
| 22 | 14.50 | 10.50 | 11.57 |
| 23 | 15.00 | 11.00 | 12.07 |
| 24 | 15.50 | 11.50 | 12.57 |
| 25 | 16.00 | 12.00 | 13.07 |
| 26 | 16.50 | 12.50 | 13.57 |
| 27 | 17.00 | 13.00 | 14.07 |

| PIN NO. | DIM. A | DIM. B | DIM. C |
|---|---|---|---|
| 28 | 17.50 | 13.50 | 14.57 |
| 29 | 18.00 | 14.00 | 15.07 |
| 30 | 18.50 | 14.50 | 15.57 |
| 31 | 19.00 | 15.00 | 16.07 |
| 32 | 19.50 | 15.50 | 16.57 |
| 33 | 20.00 | 16.00 | 17.07 |
| 34 | 20.50 | 16.50 | 17.57 |
| 35 | 21.00 | 17.00 | 18.07 |
| 36 | 21.50 | 17.50 | 18.57 |
| 37 | 22.00 | 18.00 | 19.07 |
| 38 | 22.50 | 18.50 | 19.57 |
| 39 | 23.00 | 19.00 | 20.07 |
| 40 | 23.50 | 19.50 | 20.57 |
| 41 | 24.00 | 20.00 | 21.07 |
| 42 | 24.50 | 20.50 | 21.57 |
| 43 | 25.00 | 21.00 | 22.07 |
| 44 | 25.50 | 21.50 | 22.57 |
| 45 | 26.00 | 22.00 | 23.07 |
| 46 | 26.50 | 22.50 | 23.57 |
| 47 | 27.00 | 23.00 | 24.07 |
| 48 | 27.50 | 23.50 | 24.57 |
| 49 | 28.00 | 24.00 | 25.07 |
| 50 | 28.50 | 24.50 | 25.57 |
| 51 | 29.00 | 25.00 | 26.07 |
| 52 | 29.50 | 25.50 | 26.57 |
| 53 | 30.00 | 26.00 | 27.07 |
| 54 | 30.50 | 26.50 | 27.57 |
| 55 | 31.00 | 27.00 | 28.07 |
| 56 | 31.50 | 27.50 | 28.57 |
| 57 | 32.00 | 28.00 | 29.07 |
| 58 | 32.50 | 28.50 | 29.57 |
| 59 | 33.00 | 29.00 | 30.07 |
| 60 | 33.50 | 29.50 | 30.57 |

NOTES:
1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V_0,COLOR:BLACK.
CONTACT: COPPER ALLOYS.
2.PLATING:
UNDERPLATE: 50u" NICKEL.
CONTACT AREA: 1u"GOLD OVER 50u"NICKEL.
3.MULTIMEDIA CARD COMPATIBLE

| | | | |
|---|---|---|---|
| X. ±0.50 | X.° ± 2° | UNITS mm | 广东创粤科技有限公司 |
| .X ±0.30 | .X° ± 1° | | |
| .XX ±0.10 | .XX° ± 0.5° | MAT'L | TITLE: FPC 0.5PH H2.0后掀10P |
| .XXX ± 0.05 | | | |
| THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD | | FINISH | FPC-10P-0.5PH2.0H-30242 / DWG NO.: |
| | | Q'TY | CHKD: / DR: |

| SCALE | SHEET | REV. |
|---|---|---|
| 1/1 | 1/1 | A1 |