WWW.XYECONN.COM

REV.	Q'TY	ECN. NO.	APR.	DATE







SPECIFICATION:
1.MATERIAL:
HOUSING: LCP/PA9T COLOR:BLACK
CONTACT:BRASS C2680R-H,T=0.25mm
PEG: BRASS C2680R-H,T=0.30mm
2.FINISH:
CONTACT: 1u"/3u"/5u"/5u" GOLD PLATING ON CONTACT AREA
100u" MIN. TIN PLATING ON SOLDERTAILS
30u" MIN.NICKEL UNDERPLATING OVER ALL
PEG: 100u" MIN. TIN PLATING ON SOLDERTAILS
30u" MIN.NICKEL UNDERPLATING OVER ALL







SECTION A-A



PCB LAYOUT





SECTION B-B

	耳朵要求	产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Brass C2680		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
.X:±0.30	.X°:±3°	APR. Alex	TITLE: SATA 7P 公座B型 全包开窗鱼叉 侧插式针长2.05mm
.XX:±0.20	.XX°:±2°	CHK. Jack	DWG NO. XY-SATA-7AZC-02G
.XXX:±0.05	.XXX°:±0.5°	DRA. Can	PROJ. CUSTOMER DRAWING
			SIZE A4 / SCALE 1:1 / SHEET 1/1 / REV. A

F-RD-18A