WWW.XYECONN.COM

REV.	Q'TY	ECN. NO.	APR.	DATE



SPECIFICATION:
1.MATERIAL:
HOUSING: LCP UL 94V-0
COLOR:BLACK
CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm
PEG:C2680R-H,T=0.50mm
2.FINISH:
CONTACT:1u"/3u"/5u"/15u" GOLDPLATING ON CONTACT AREA
100u"TIN PLATING ON SOLDERTAILS
30u"NICKEL UNDERPLATING OVER ALL
PEG: 100u" TIN PLATING ON SOLDERTAILS
30u"NICKEL UNDERPLATING OVER ALL







剖面A-A



剖面B-B



RECOMMENDED PCB LAYOUT
PCB TOLERANCE:±0.05







	环保要求	产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
.X:±0.30	.X°:±3°	APR. Alex	TITLE: SATA 7+15P 母座 DIP 180° 双排双鱼叉加长型针长2.7
.XX:±0.20	.XX°:±2°	CHK. Jack	DWG NO. XY-SATA-22AZC-13M
.XXX:±0.05	.XXX°:±0.5°	DRA. Can	PROJ. CUSTOMER DRAWING
			SIZE A4 / SCALE 1:1 / SHEET 1/1 / REV. A

F-RD-18A