WWW.XYECONN.COM

REV.	Q'TY	ECN. NO.	APR.	DATE





SECTION C–C



SECTION A–A





SECTION B–B





P.C.B Layout

SPECIFICATION:

1.MATERIAL:

HOUSING:LCP 30% G/F UL 94V–0

COLOR:BLACK

CONTACT:BRASS C2680R–H,T=0.25mm

2.FINISH:

CONTACT:1u",3u",5u",15u"30u"GOLD PLATING ON CONTACT AREA

100u" MIN.TIN PLATING ON SOLDERTAILS

40u" MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:

CURRENT RATING:1.5 AMPERE PER CONTACT

CONTACT RESISTANCE:30 MILLIOHMS MAX

INSULATION RESISTANCE:1000 MEGOHMS MIN

DIELECTRIC WITH STANDING VOVTAGE:500 VDC

OPERATING TEMPERATURE: –40°C ~ +85°C



环保要求		产品必须符合ROHS要求		
2	Terminal	BRASS C2680R–H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V–0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
.X:±0.30	.X°:±3°	APR. Alex	TITLE: SATA 7+15P 夹角公座 夹板1.0七个孔
.XX:±0.20	.XX°:±2°	CHK. Jack	DWG NO. XY–SATA–22BCC–07G
.XXX:±0.05	.XXX°:±0.5°	DRA. Can	PROJ. CUSTOMER DRAWING
			SIZE A4 SCALE 1:1 SHEET 1/1 REV. A

F–RD–18A