REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		

RoHS Compliant









Specifications:

1. Rated Voltage : 250V AC/DC
2. Rated Current : 2A AC,DC
3. Withstand Voltage : 1000V AC/minute
4. Contact Resistance : 50mΩ(MAX.)
5. Insulation Resistance : 1000MΩ(MIN.)
6. Storage Temperature Range:-40°C~+85°C;
7. Operation Temperature Range:-25°C~+70°C;

PIN数	A±0.1	B±0.1	C±0.1
2P	8.00	4.75	2.00
3P	10.00	6.75	4.00
4P	12.00	8.75	6.00
5P	14.00	10.75	8.00
6P	16.00	12.75	10.00
7P	18.00	14.75	12.00
8P	20.00	16.75	14.00
9P	22.00	18.75	16.00
10P	24.00	20.75	18.00



立贴加盖视图



序号	品 名	材 质	电镀／颜色	备 注
C	插片	黄铜	镀镍锡	
B	插针	黄铜	镀镍锡	
A	基座	LCP	本 色	



RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE±0.1)



3D VIEW

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°		
.XX ±0.10	.XX° ± 0.5°	MAT'L	TITLE: PH2.0 立贴针座
.XXX ± 0.05			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	APPD:
		Q'TY	CHKD:
			DR:

DWG NO.: CY-PH2.0-2P-SMT-46874

SCALE	SHEET	REV.
1/1	1/1	A1