
RoHS

目錄 MAPX	设变内容 MODIFICATION	日期 DATE




1.MATERIAL:
INSULATOR: PBT+ 30% GLASS FIBER
Color:Black\White\Blue
TERMINAL: COPPER ALLOY
GOLD FLASH ON CONTACT AREA
SN:100U" ON SOLDER TAIL
NICKEL:50U" ON THE BASE
SHELL: Shell Plated:Cu50u"/Ni100u"
and Cu50u"/Sn100u"

2.ELECTRICAL:
INSULATOR RESISTANCE: 1000MEGOHMS MIN. 500V DC.
DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC R.M.S
VOLTAGE TATING: 40V AC (RMS) CONTINUOUS MAX.
CURRENT RATING: 5A.
CONTGACT RESISTANCE: 20 MILLIOHMS MAX.


3.ENVIRONMENTAL
TEMPERATURE RANGE:-25°C TO + 85°C.

4.MECHANICAL
MATING FORCE:DB 9Pin(6.0Kgf Max),DB 15Pin(6.5Kgf Max).
DB 25Pin(9.47Kgf Max),DB 37Pin(13.55Kgf Max).
UNMATING FORCE:DB 9Pin(0.9Kgf Min),DB 15Pin(1.2Kgf Min)
DB 25Pin(1.5Kgf Min),DB 37Pin(1.8Kgf Min)


5.HOW TO ORDER




Rivet option:
Type A:前铆实芯螺母



Rivet option:
Type B:后铆4.0空芯螺母



Rivet option:
Type C:前铆空芯螺母



Rivet option:
Type X: 铆合无螺丝

DIM \ PIN	9Pin	15Pin	25Pin	37Pin
Dim:A	30.80	39.20	53.05	69.40
Dim:B	25.00	33.30	47.05	63.50
Dim:C	16.30	24.70	38.40	54.80
Dim:D	19.20	27.70	41.10	57.30
Dim:E	10.60	10.70	10.70	10.70

产品图
PRODUCT CHART DWG

公差一览表
TOLERANCE UNLESS OTHERWISE

X.	±0.35	X°.	±5°
.X	±0.30	.X°	±2°
.XX	±0.25	.XX°	±1°
.XXX	±0.10	.XXX°	±0.5°

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	Erick	产品料号 PRODUCT PART NO.	920-H0108051Y00101
比例 SCALE	1:1	审核 CHKD	L S S	产品名称 PRODUCT NO.	DB-母头9PIN焊线式铁壳PB蓝胶48H
日期 DATE	2021/03/10	核准 APPD	黄国荣	角法 VIEW	版本 VER A0

您正在使用 ZWCAD 2022 个人版，不得用于商业用途， 详情请咨询4007-182-588。