


RoHS

| 目錄 MAPX | 设变内容 MODIFICATION | 日期 DATE |
|---|---|---|
| | | |





铆合




后铆螺母




NOTICE :

1. ELECTRICE:
   - DIELECTRIC RATING: 300V
   - CONTACT CURRENT RATING: 3AMP
   - CONTACT RESISTANCE: 15mΩ MAX.
   - INSULATION RESISTANCE: 1000MΩ MIN.AT 500V DC
   - DIELECTRIC STRENGTH: 500V AC RMS FOR 1MINUTE

   OPERATION TEMPERATURE: -55C° ～125C°
2. MATERIAL:
   - INSULATOR: PBT+30% G.F(UL94V-0)
   - CONTACT: COPPER ALLOY
   - CONTACT PLATED:GOLD FIASH OVER NICKEL
   - SHELL: SPCC
   - SHELL PLATED:NICKEL/TIN

| PO(XXX) | A ±0.25 | B ±0.13 | C ±0.38 | D ±0.25 |
|---|---|---|---|---|
| 015 | 16.33 | 24.99 | 30.81 | 19.28 |
| 026 | 24.66 | 33.32 | 39.14 | 27.51 |
| 044 | 38.38 | 47.04 | 53.04 | 41.28 |

产品图 PRODUCT CHART DWG

公差一览表 TOLERANCE UNLESS OTHERWISE

| | | | |
|---|---|---|---|
| X. | ±0.35 | X°. | ±5° |
| .X | ±0.30 | .X° | ±2° |
| .XX | ±0.25 | .XX° | ±1° |
| .XXX | ±0.10 | .XXX° | ±0.5° |

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

| | | | | | |
|---|---|---|---|---|---|
| 单位 UNITS | MM | 制图 DRAWING | Erick | 产品料号 PRODUCT PART NO. | 920-H6101010Y10004 |
| 比例 SCALE | 1:1 | 审核 CHKD | L S S | 产品名称 PRODUCT NO. | HDB 母头26PIN车针焊线式传统铆合款铁壳PBT白胶48H |
| 日期 DATE | 2021/03/10 | 核准 APPD | 黄国荣 | 角法 VIEW | 版本 VER A0 |

您正在使用 ZWCAD 2022 个人版，不得用于商业用途， 详情请咨询4007-182-588。