www.dzyjzj.com Tel:0755-27575531 Fax:0755-27576267





PIN	ø1.1	ø1.3
APPD.		



P.C.B LAYOUT
TOP VIEW

SCHEMATIC

DC-002	DC-002-1
	

SPECIFICATION

1. Rating : DC 30V 1.0A;
2. Contact resistance: ≤0.03Ω;
3. Insulation resistance: ≥100MΩ (DC250V);
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 3-20N;
6. life test: 5,000 cycles。

NO.	DESCRIPTION	QTY	MATERIAL	PLATING
6	PIN	1	H59 BRASS	Ni-Plating
5	CURVE PIECE	1	H62 BRASS	Ag-Plating
4	FLAT PIECE	1	H62 BRASS	Ag-Plating
3	SPRING	1	SUS301	Ag-Plating
2	COVER	1	PBT	
1	HOUSING	1	PBT	

深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30, X.XX ±0.25, X.XXX ±0.15, X.° ±2°, X.X° ±0.5°	DRAWED BY : 陈一鸣	DATE : 2014-02-23	PART NAME: DC-002
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW02-DC002-XXXB
UNIT: mm [inch]	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO. / DRAW NO. HYC-2610151629
SCALE:1:1 SIZE: A4			SHEET NO. 1 OF 1