产 品 规 格 书
Product Specification

CUSTOMER	客户:	
CUSTOMER PN	客户 PN:	
HANG CRYSTAL P/N	杭晶物料编码:	**CFUMT6-45.000-F30IL03BL**
MODEL	产品型号:	**Crystal Filter UM-1 X 2, 45.000MHz**
NOMINAL FREQUENCY	频率:	**45.000MHz**
ISSUE DATE	日期:	**2017 /06 / 06**

CUSTOMER'S APPROVAL
客户确认

(PLEASE RETURN A COPY WITH APPOVAL)
（请将确认的复印件返回我司）

APPROVED	QA
MB.	James J


SUZHOU HANGJING ELEC&TECH CO.,LTD
苏州杭晶电子科技有限公司
No. 207, Blk. B, Chenlei Science & Technology Park, No. 1, First Qunxing Road, Suzhou Industrial Park, Jiangsu, China
TEL.86 (0)512 65916689
FAX 86 (0)512 65918005

Revision	Description / ECN	Prepared	Approved	Date
1	Initial release	MB.	James Jiang	2017-06-06
2	Not issued			
3	Not issued			
4	Not issued			

1. ELECTRICAL SPECIFICATIONS

No	Item	Spec.
1	Model	45M15B
2	Center Frequency	45.000MHz
3	Pass Band Width at 3dB	≥±15kHz
4	Insertion Loss	≤3.0dB
5	Ripple	≤1.0dB
6	Stop Band Width at 30dB	≤±40kHz
9	Terminating Impedance	1200Ω//0.5pF （实际匹配为准）
10	Insulation Resistance	≥500MΩ @DC 500V
11	Operating Temperature Range	-20℃~+70℃
12	Storage Temperature Range	-40℃~+85℃
13	Package	UM-1 X 2

2. DIMENSIONS (Unit: mm)



3. Test Circuit

