产 品 规 格 书
Product Specification

CUSTOMER	客户:	
CUSTOMER PN	客户 PN:	
HANG CRYSTAL P/N	杭晶物料编码:	**CFMH4-10.000-F01IL4.5EL**
MODEL	产品型号:	**Crystal Filter 30x20x10**
NOMINAL FREQUENCY	频率:	**10.000MHz**
ISSUE DATE	日期:	**2020/02/04**

CUSTOMER'S APPROVAL
客户确认

(PLEASE RETURN A COPY WITH APPOVAL)
（请将确认的复印件返回我司）

APPROVED	QA
MB.	James J

SUZHOU HANGJING ELEC&TECH CO.,LTD
苏州杭晶电子科技有限公司
No. 207, Blk. B, Chenlei Science & Technology Park, No. 1, First Qunxing Road, Suzhou Industrial Park, Jiangsu, China
TEL.86 (0)512 65916689
FAX 86 (0)512 65918005

Revision	Description / ECN	Prepared	Approved	Date
A	Initial release	MB.	James Jiang	2020-02-04
B	Not issued			
C	Not issued			
D	Not issued			

1. ELECTRICAL SPECIFICATIONS

No	Item	Spec.
1	Center Frequency	10.000MHz
2	Pole	6
3	Pass Band Width at 3dB	≥±500Hz
4	Insertion Loss	≤4.5dB
5	Ripple	≤1.0dB
6	Restraint Outside the Band	≥60dBc @F0±5kHz
7	Input Level	≤10dBm
8	Input/output Impedance	50Ω
9	Operating Temperature Range	-40℃~+ 85℃
10	Storage Temperature Range	-55℃~+ 125℃
11	Size	30x20x10

2. DIMENSIONS (Unit: mm)

