TACT SWITCH

碩方精密電子開關 www.Sofng.com

Operation: SMT/立贴式 微型 轻触开关 [操作力可定制]

RoHS Compliant

LTEM NO.: TS-1822C-16Q (Series)

(L3.0mm×W2.5mm×W1.5mm TACT-SWITCH)


表面贴装 SMT

正向操作

精密部品 NICETY

可靠 STABILIZE

適合環保 RoHS



邀您使用(微信)小程序

硕方电子开关&连接器选型手册

手机扫码即可进入...


Material declaration

No	NAME	Description
A	基座 CASE	LCP 30%G/F (Gray)耐热塑胶
B	端子 Fixed Ccontact	C5191R-H (t=0.10mm)磷青铜【30u" 锡基】
C	簧片 Moving Ccontact	接触面镀银&不锈钢 SUS304
D	腹膜层 Sticker layer	TI 聚酰亚胺 Polyimide
E	按柄 Stem	PA46 尼龙 (TW271F6)无卤塑胶
F	外壳 Cover	SUS301-3/4H(t=0.15mm)不锈钢


Technical parameter


PROJECT \ LEVEL		A[better product]	B[average product]
Electrical Properties	Contact Rating	25mA, 24V DC	
	Initial Contact Resistance	50mΩ max.	
	Insulation Resistance	100MΩ min.500V DC Skey/PD：100MΩ min.300V DC	
	Withstand Voltage	300V AC for 1 minute	250 V AC for 1 minut
Durable Performance	There No Load	65,000 Cycles	50,000 Cycles
	Rated Load	50,000 Cycles	40,000 Cycles
Sterage temp.		-35℃～+75℃(Operating Temp:)	
Operating Force		1.6 / 2.6N. (1N.=100gram-force)	
Heat Rrsistance		IR Reflow:255℃,5sec. Manual:350℃,3sec.	


CIRCUIT DIAGRAM





Unit:mm














P.C.B LAYOUT

