










RECOMMENDED PCB LAYOUT (TOP VIEW)

TOLERANCES:±0.05

Notes：

Rated current:3.0A

Withstand Voltage:500V AC/DC

Contact Resistance:20mΩ Max

Insulation Resistance:1000MΩ Min

Operating Temperature:-40℃ TO +105℃

Contact Material:Brass

Platin :G/F

Insulator Material: PA6T UL94V-0 BK

———		new		2015/5/3		A	瀚源
ECN BO.		DESCRIPTION.		DATE.		REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2	SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	2541WVS-2xXXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°
			MODEL NAME	2541WVS-2xXXP			
			3RD ANGLE PROJ	HanElectricity Co.,LTD			FILE.NO.