




Kinghelm®











SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

型号-极数 TYPE-Poles	尺寸Dimensions(mm) A	B	C
A2501A-2P	2.50	7.50	6.00
A2501A-3P	5.00	10.00	8.50
A2501A-4P	7.50	12.50	11.00
A2501A-5P	10.00	15.00	13.50
A2501A-6P	12.50	17.50	16.00
A2501A-7P	15.00	20.00	18.50
A2501A-8P	17.50	22.50	21.00
A2501A-9P	20.00	25.00	23.50
A2501A-10P	22.50	27.50	26.00
A2501A-11P	25.00	30.00	28.50
A2501A-12P	27.50	32.50	31.00
A2501A-13P	30.00	35.00	33.50
A2501A-14P	32.50	37.50	36.00
A2501A-15P	35.00	40.00	38.50
A2501A-16P	37.50	42.50	41.00
A2501A-17P	40.00	45.00	43.50
A2501A-18P	42.50	47.50	46.00

SPECIFICATION

1 Material:
  Insulator: PA66 (UL94V-1)
  Contacts: Brass, Tin-plated
2 Contact resistance: ≤20mΩ
3 Insulation resistance: ≥1000MΩ
4 Rated voltage: 250 V AC DC
5 Rated current: 3.0 A AC DC
6 Withstand Voltage: 1000V AC/minute
7 Temperature Range: -25℃ ~ +85℃
8 Six deleterious substance content meet the environmental protection requirement

REV	DESCRIPTION	REV. DRAWN	DATE
A	NEW RELEASE		

TOLERANCE	SCALE:
. ±0.25	UNIT: mm
*.** ±0.15	VIEW:
*.*** ±0.05	
DRAW	
CHECK	
APPRO	

PART NO: KH-XH-6A-Z

TITLE: 2.50mm PITCH 180° WAFER

XH直针

深圳市金航标电子有限公司
www.kinghelm.com.cn 0755-83044319