









带@符号为重点尺寸，



PART NO	Dim. A	Dim. B
2.0-2*4P	6.0	13.2
2.0-2*5P	8.0	15.2
2.0-2*6P	10.0	17.2
2.0-2*7P	12.0	19.2
2.0-2*8P	14.0	21.2
2.0-2*9P	16.0	23.2
2.0-2*10P	18.0	25.2
2.0-2*11P	20.0	27.2
2.0-2*12P	22.0	29.2
2.0-2*13P	24.0	31.2
2.0-2*14P	26.0	33.2
2.0-2*15P	28.0	35.2
2.0-2*17P	32.0	39.2
2.0-2*18P	34.0	41.2
2.0-2*20P	38.0	45.2
2.0-2*22P	42.0	49.2
20-2*25P	48.0	55.2
2.0-2*28P	54.0	61.2



MATERIAL&FINISH

"H"Insulator:PBT Glass Fiber(UL94V-0)

"M"Insulator:PA66 Glass Fiber(UL94V-0)

"SR"Insulator:PA66 Glass Fiber(UL94V-0)

Contact : Brass

Contact :Gold-Plated Over Nickel.

SPECIFICATIONS

Current Rating :1A AC,DC

Voltage Rating:250V AC,DC

Temperature Range:-40°C To+105°C

Contact Resistance:20mΩ Min

Insulation Resistance:1000MΩ Min

Withstanding Voltage:500V AC/Min

UNLESS OTHERWISE SPECIFIED TOLERANCE: x ±0.25 ANGLES:±z .XX ±0.15 XX ±0.10 Do NOT SCAL DAWwo		浙江博穆电子精密科技有限公司			
DRAWN BY	唐建华	2.0-2*NP压线头			003
CHECKED BY		SIZE A	UNIT MM	PART NO. CSD-WI-EG-OA-003	REV A
APPROVED BY		SCALE		THIRD ANOLE PROJECTION	PAGE 1 oF 1
DWG NO.				TLH NO.	DATOT9/07/2006