

High-Speed HDMI with Ethernet All-in-One Keystone/Panel Mount Coupler Cable (F/F), Angled Connector, 1 ft. (0.31 m)

MODEL NUMBER: P164-001-KPA-BK



Adds an HDMI female port to a fixed location, such as a universal keystone wallplate, panel, podium or kiosk. Gives your conference room, classroom, home theater room or retail establishment a professional, clutter-free look.

Features

Mounts an HDMI Port in a Fixed Location

- Keystone design for easy snap-in installation in wallplate or panel
- Includes panel mount adapter for installation in podium or kiosk
- Angled female connector for easy installation in tight spaces
- Molded gold-plated connectors for optimum signal transfer
- Hides components out of sight to eliminate cable clutter
- Compatible with all HDMI cables

Premium Construction for Superior Signal Transfer

- Premium foil shielding for error-free signal quality and EMI/RFI protection
- Molded gold-plated connectors
- Integral strain relief for long life
- Rugged PVC jacket

Specifications

OVERVIEW	
UPC Code	037332195746
Technology	HDMI
CONNECTIONS	

Highlights

- Connects 2 HDMI devices, such as Blu-ray™ players and monitors
- Panel mount adapter for securing to podium or kiosk
- Molded gold-plated connectors for optimal signal transfer
- Superior foil shielding for EMI/RFI protection
- Angled female connector for easy installation in tight spaces

Package Includes

- P164-001-KPA-BK High-Speed HDMI All-in-One Keystone/Panel Mount Coupler Cable (F/F), 1 ft.



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Cable Length (cm)	30.48
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.