

Specification Sheet

Part Number: 558-00308



Pre-printed header striped continuous vinyl rolls come in different header colors, providing a variety of printing options.

The headers can be printed with various ARC FLASH, WARNING And CAUTION headlines to meet OSHA safety standards for identifying electrical panels and equipment.

Signs can be designed in TagPrint Pro labeling software and printed with any HellermannTyton thermal transfer printing system with optional cutter attached.

Thermal Transfer Adhesive Labels, Solid Color Continuous Roll, 1.0 x 250', UV Stable VL, Red, 250 ft/roll

Article Number 558-00308

Type HT1RD250

Color Red (RD)

Quantity Per roll

Product Description Continuous Vinyl Labels are made with UV-stable materials for long outdoor life. The labels are extruded in the actual color and not colored using surface inks for long-term fade resistance. Vinyl labels are provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems. Good for all surface types except powder coat painted or low surface energy substrates such as polypropylene. Test on these surfaces before approving.

Short Description	Thermal Transfer Adhesive Labels, Solid Color Continuous Roll, 1.0 x 250', UV Stable VL, Red, 250 ft/roll
Global Part Name	HT1RD250-1500-RD
Length L (Imperial)	250.0
Length L (Metric)	76.20
Variant	3.2mil, 50lb bleached kraft paper
Width W (Imperial)	1.0
Width W (Metric)	25.40
Thickness T (Metric)	64.0
Width of Liner (Metric)	25.40
Width of Liner (Imperial)	1.0
Material	Type 1500, Vinyl, UV-stabilized, glossy (1500)
Material Shortcut	1500
Adhesive	Acrylic
Halogen Free	No

UV Resistant (Yes/No)	Yes
Adhesive Operating Temperature	-40°F to +180°F (-40°C to +82°C)
Operating Temperature	-40°F to +180°F (-40°C to +82°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2020 NEC2011 NEC2017 NEC2014 NEC2023
Package Quantity (Imperial)	250
Package Quantity (Metric)	76.20
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

