

Specification Sheet

Part Number: 155-05400



Oval mount design pushes on easy by hand without the need for tools. Design provides low insertion and high extraction force.

1-Pc Cable Tie/Oval Stud Mount, Designed for 5.0 mm stud, 6.0" Long, PA66HS, Black, 500/pkg

Article Number	155-05400
----------------	-----------

Type	T50SOSSB5-HIGH-E
------	------------------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	The special oval shape provides for an approximate .20" (5.0 mm) lateral adjustment, allowing for any misalignment of the stud or incorrect positioning of the tie on the cables
---------------------	--

Short Description	1-Pc Cable Tie/Oval Stud Mount, Designed for 5.0 mm stud, 6.0" Long, PA66HS, Black, 500/pkg
-------------------	---

Global Part Name	T50SOSSB5-HIGH-E-PA66HS-BK
------------------	----------------------------

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	170
Length L (Imperial)	6.0
Length L (Metric)	160
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.19
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.04
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	1.4
Bundle Diameter Max (Metric)	35.0
Thickness T (Imperial)	0.05

Thickness T (Metric)	1.35
Stud Length Max (Imperial)	0.63
Stud Length Max (Metric)	16.0
Stud Length Min (Metric)	11.0
Stud Diameter (Metric)	5.0 mm
Stud Diamater (Imperial)	0.2
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).