




[illegible]

A

10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																										
△₃ 適合製品及び各種仕様書 APPLICABLE PRODUCTS AND VARIOUS SPECIFICATIONS <table><tr><td rowspan="2">梱包仕様書 PACKAGING SPECIFICATION</td><td>PART NUMBER</td><td>SPECIFICATION NUMBER</td></tr><tr><td>204532**0*</td><td>2045329200 PS 200</td></tr></table> <table><tr><td rowspan="3">適合ターミナル APPLICABLE TERMINAL</td><td>PART NUMBER</td><td>PLATING TYPE</td><td>WIRE SIZE(AWG)</td></tr><tr><td>5054311000</td><td>TIN</td><td rowspan="2">#26-30</td></tr><tr><td>5054311100</td><td>GOLD</td></tr></table> SMT <table><tr><td rowspan="3">適合嵌合相手 MATE WITH</td><td rowspan="2">タイプ TYPE</td><td colspan="3">TIN PLATING</td><td colspan="2">GOLD PLATING</td></tr><tr><td>VERTICAL</td><td>RIGHT ANGLE</td><td>VERTICAL (FOR POTTING)</td><td>VERTICAL</td><td>RIGHT ANGLE</td></tr><tr><td colspan="5">2-16 CIRCUIT</td><td></td><td></td></tr><tr><td rowspan="2"></td><td rowspan="4">製品番号 PART NUMBER</td><td>204530**7*</td><td>204529**7*</td><td>205957**7*</td><td>204530**** 3, 5, 8▲</td><td>204529**** 3, 5, 8▲</td></tr><tr><td colspan="2"></td><td></td><td></td><td></td></tr><tr><td colspan="2">製品仕様書 PRODUCT SPECIFICATION</td><td colspan="2">2045320000-PS PS 000</td><td>2045320001-PS PS 000</td><td>2045320000-PS PS 001</td></tr><tr><td colspan="2">コネクタ取扱説明書 APPLICATION SPECIFICATION</td><td colspan="4">5055650000-AS PS 000</td></tr></table> THROUGH HOLE <table><tr><td rowspan="3">適合嵌合相手 MATE WITH</td><td rowspan="2">タイプ TYPE</td><td colspan="2">TIN PLATING</td></tr><tr><td>VERTICAL</td><td>RIGHT ANGLE</td></tr><tr><td colspan="2">2-16 CIRCUIT</td><td></td></tr><tr><td rowspan="2"></td><td rowspan="4">製品番号 PART NUMBER</td><td>220097**7*</td><td>220098**7*</td></tr><tr><td colspan="2"></td></tr><tr><td colspan="2">製品仕様書 PRODUCT SPECIFICATION</td><td colspan="2">2045320002-PS PS 000</td></tr><tr><td colspan="2">コネクタ取扱説明書 APPLICATION SPECIFICATION</td><td colspan="2">5055650000-AS PS 000</td></tr></table> WIRE TO WIRE <table><tr><td rowspan="3">適合嵌合相手 MATE WITH</td><td rowspan="2">タイプ TYPE</td><td>TIN PLATING</td></tr><tr><td>2-9 CIRCUIT</td></tr><tr><td>製品番号 PART NUMBER</td><td>2145252***</td></tr><tr><td colspan="2">製品仕様書 PRODUCT SPECIFICATION</td><td>5055650003-PS PS 000</td></tr><tr><td colspan="2">コネクタ取扱説明書 APPLICATION SPECIFICATION</td><td>5055650000-AS PS 000</td></tr></table> 製品嵌合図は各嵌合相手図面を参照のこと MATING VIEW : REFER TO EACH "MATE WITH" PART DRAWING. △₄ 204532**0* 発注番号一覧 ORDER NUMBER LIST <table><tr><td>BLACK</td><td>NATURAL (WHITE)</td><td>HOUSING COLOR</td></tr><tr><td>2045321601</td><td>2045321600</td><td>16</td></tr><tr><td>2045321501</td><td>2045321500</td><td>15</td></tr><tr><td>2045321401</td><td>2045321400</td><td>14</td></tr><tr><td>2045321301</td><td>2045321300</td><td>13</td></tr><tr><td>2045321201</td><td>2045321200</td><td>12</td></tr><tr><td>2045321101</td><td>2045321100</td><td>11</td></tr><tr><td>2045321001</td><td>2045321000</td><td>10</td></tr><tr><td>2045320901</td><td>2045320900</td><td>9</td></tr><tr><td>2045320801</td><td>2045320800</td><td>8</td></tr><tr><td>2045320701</td><td>2045320700</td><td>7</td></tr><tr><td>2045320601</td><td>2045320600</td><td>6</td></tr><tr><td>2045320501</td><td>2045320500</td><td>5</td></tr><tr><td>2045320401</td><td>2045320400</td><td>4</td></tr><tr><td>2045320301</td><td>2045320300</td><td>3</td></tr><tr><td>2045320201</td><td>2045320200</td><td>2</td></tr><tr><td colspan="2">発注番号 ORDER NUMBER</td><td rowspan="2">極数 CIRCUIT SIZE</td></tr><tr><td colspan="2">梱包形態：ポリ袋 PACKAGING：POLYBAG PACKAGE</td></tr></table> <table><tr><td colspan="10">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr><tr><td rowspan="2">DIMENSION UNITS</td><td colspan="2">SCALE</td><td colspan="4" rowspan="2">CURRENT REV DESC:</td><td colspan="3" rowspan="2">molex</td></tr><tr><td>mm</td><td>NTS</td></tr><tr><td colspan="3">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="4" rowspan="5">EC NO: 757367 DRWN: SOKUMURA01 2023/07/21 CHK'D: SAKIYAMA 2023/09/12 APPR: AIDA 2023/09/12 INITIAL REVISION: DRWN: RWATANABE01 2017/09/15 APPR: TKANEKO 2017/09/26</td><td colspan="3">MICRO-LOCK PLUS 1.25 W/B SINGLE ROW RECEPTACLE HOUSING LOW-HALOGEN</td></tr><tr><td>ANGULAR TOL</td><td>±</td><td>3.0°</td><td colspan="3">PRODUCT CUSTOMER DRAWING</td></tr><tr><td>4 PLACES</td><td>±</td><td>0.2</td><td colspan="3">DOCUMENT NUMBER</td></tr><tr><td>3 PLACES</td><td>±</td><td>0.2</td><td colspan="3">2045320000-SD</td></tr><tr><td>2 PLACES</td><td>±</td><td>0.2</td><td>DOC TYPE</td><td>DOC PART</td><td>REVISION</td></tr><tr><td>1 PLACE</td><td>±</td><td>0.2</td><td colspan="4"></td><td>PSD</td><td>000</td><td>G</td></tr><tr><td>0 PLACES</td><td>±</td><td>0.2</td><td colspan="4"></td><td colspan="3"></td></tr><tr><td colspan="3">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>THIRD ANGLE PROJECTION</td><td>DRAWING</td><td>SERIES</td><td>MATERIAL NUMBER</td><td colspan="2">CUSTOMER</td><td>SHEET NUMBER</td></tr><tr><td colspan="3"></td><td></td><td>A3-SIZE</td><td>204532</td><td>SEE CHART</td><td colspan="2">GENERAL</td><td>3 OF 3</td></tr></table>										梱包仕様書 PACKAGING SPECIFICATION	PART NUMBER	SPECIFICATION NUMBER	204532**0*	2045329200 PS 200	適合ターミナル APPLICABLE TERMINAL	PART NUMBER	PLATING TYPE	WIRE SIZE(AWG)	5054311000	TIN	#26-30	5054311100	GOLD	適合嵌合相手 MATE WITH	タイプ TYPE	TIN PLATING			GOLD PLATING		VERTICAL	RIGHT ANGLE	VERTICAL (FOR POTTING)	VERTICAL	RIGHT ANGLE	2-16 CIRCUIT								製品番号 PART NUMBER	204530**7*	204529**7*	205957**7*	204530**** 3, 5, 8▲	204529**** 3, 5, 8▲						製品仕様書 PRODUCT SPECIFICATION		2045320000-PS PS 000		2045320001-PS PS 000	2045320000-PS PS 001	コネクタ取扱説明書 APPLICATION SPECIFICATION		5055650000-AS PS 000				適合嵌合相手 MATE WITH	タイプ TYPE	TIN PLATING		VERTICAL	RIGHT ANGLE	2-16 CIRCUIT				製品番号 PART NUMBER	220097**7*	220098**7*			製品仕様書 PRODUCT SPECIFICATION		2045320002-PS PS 000		コネクタ取扱説明書 APPLICATION SPECIFICATION		5055650000-AS PS 000		適合嵌合相手 MATE WITH	タイプ TYPE	TIN PLATING	2-9 CIRCUIT	製品番号 PART NUMBER	2145252***	製品仕様書 PRODUCT SPECIFICATION		5055650003-PS PS 000	コネクタ取扱説明書 APPLICATION SPECIFICATION		5055650000-AS PS 000	BLACK	NATURAL (WHITE)	HOUSING COLOR	2045321601	2045321600	16	2045321501	2045321500	15	2045321401	2045321400	14	2045321301	2045321300	13	2045321201	2045321200	12	2045321101	2045321100	11	2045321001	2045321000	10	2045320901	2045320900	9	2045320801	2045320800	8	2045320701	2045320700	7	2045320601	2045320600	6	2045320501	2045320500	5	2045320401	2045320400	4	2045320301	2045320300	3	2045320201	2045320200	2	発注番号 ORDER NUMBER		極数 CIRCUIT SIZE	梱包形態：ポリ袋 PACKAGING：POLYBAG PACKAGE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										DIMENSION UNITS	SCALE		CURRENT REV DESC:				molex			mm	NTS	GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 757367 DRWN: SOKUMURA01 2023/07/21 CHK'D: SAKIYAMA 2023/09/12 APPR: AIDA 2023/09/12 INITIAL REVISION: DRWN: RWATANABE01 2017/09/15 APPR: TKANEKO 2017/09/26				MICRO-LOCK PLUS 1.25 W/B SINGLE ROW RECEPTACLE HOUSING LOW-HALOGEN			ANGULAR TOL	±	3.0°	PRODUCT CUSTOMER DRAWING			4 PLACES	±	0.2	DOCUMENT NUMBER			3 PLACES	±	0.2	2045320000-SD			2 PLACES	±	0.2	DOC TYPE	DOC PART	REVISION	1 PLACE	±	0.2					PSD	000	G	0 PLACES	±	0.2								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER		SHEET NUMBER					A3-SIZE	204532	SEE CHART	GENERAL		3 OF 3									
梱包仕様書 PACKAGING SPECIFICATION	PART NUMBER	SPECIFICATION NUMBER																																																																																																																																																																																																																																																																	
	204532**0*	2045329200 PS 200																																																																																																																																																																																																																																																																	
適合ターミナル APPLICABLE TERMINAL	PART NUMBER	PLATING TYPE	WIRE SIZE(AWG)																																																																																																																																																																																																																																																																
	5054311000	TIN	#26-30																																																																																																																																																																																																																																																																
	5054311100	GOLD																																																																																																																																																																																																																																																																	
適合嵌合相手 MATE WITH	タイプ TYPE	TIN PLATING			GOLD PLATING																																																																																																																																																																																																																																																														
		VERTICAL	RIGHT ANGLE	VERTICAL (FOR POTTING)	VERTICAL	RIGHT ANGLE																																																																																																																																																																																																																																																													
	2-16 CIRCUIT																																																																																																																																																																																																																																																																		
	製品番号 PART NUMBER	204530**7*	204529**7*	205957**7*	204530**** 3, 5, 8▲	204529**** 3, 5, 8▲																																																																																																																																																																																																																																																													
製品仕様書 PRODUCT SPECIFICATION		2045320000-PS PS 000		2045320001-PS PS 000	2045320000-PS PS 001																																																																																																																																																																																																																																																														
コネクタ取扱説明書 APPLICATION SPECIFICATION		5055650000-AS PS 000																																																																																																																																																																																																																																																																	
適合嵌合相手 MATE WITH	タイプ TYPE	TIN PLATING																																																																																																																																																																																																																																																																	
		VERTICAL	RIGHT ANGLE																																																																																																																																																																																																																																																																
	2-16 CIRCUIT																																																																																																																																																																																																																																																																		
	製品番号 PART NUMBER	220097**7*	220098**7*																																																																																																																																																																																																																																																																
製品仕様書 PRODUCT SPECIFICATION		2045320002-PS PS 000																																																																																																																																																																																																																																																																	
コネクタ取扱説明書 APPLICATION SPECIFICATION		5055650000-AS PS 000																																																																																																																																																																																																																																																																	
適合嵌合相手 MATE WITH	タイプ TYPE	TIN PLATING																																																																																																																																																																																																																																																																	
		2-9 CIRCUIT																																																																																																																																																																																																																																																																	
	製品番号 PART NUMBER	2145252***																																																																																																																																																																																																																																																																	
製品仕様書 PRODUCT SPECIFICATION		5055650003-PS PS 000																																																																																																																																																																																																																																																																	
コネクタ取扱説明書 APPLICATION SPECIFICATION		5055650000-AS PS 000																																																																																																																																																																																																																																																																	
BLACK	NATURAL (WHITE)	HOUSING COLOR																																																																																																																																																																																																																																																																	
2045321601	2045321600	16																																																																																																																																																																																																																																																																	
2045321501	2045321500	15																																																																																																																																																																																																																																																																	
2045321401	2045321400	14																																																																																																																																																																																																																																																																	
2045321301	2045321300	13																																																																																																																																																																																																																																																																	
2045321201	2045321200	12																																																																																																																																																																																																																																																																	
2045321101	2045321100	11																																																																																																																																																																																																																																																																	
2045321001	2045321000	10																																																																																																																																																																																																																																																																	
2045320901	2045320900	9																																																																																																																																																																																																																																																																	
2045320801	2045320800	8																																																																																																																																																																																																																																																																	
2045320701	2045320700	7																																																																																																																																																																																																																																																																	
2045320601	2045320600	6																																																																																																																																																																																																																																																																	
2045320501	2045320500	5																																																																																																																																																																																																																																																																	
2045320401	2045320400	4																																																																																																																																																																																																																																																																	
2045320301	2045320300	3																																																																																																																																																																																																																																																																	
2045320201	2045320200	2																																																																																																																																																																																																																																																																	
発注番号 ORDER NUMBER		極数 CIRCUIT SIZE																																																																																																																																																																																																																																																																	
梱包形態：ポリ袋 PACKAGING：POLYBAG PACKAGE																																																																																																																																																																																																																																																																			
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																																																																																																																																																			
DIMENSION UNITS	SCALE		CURRENT REV DESC:				molex																																																																																																																																																																																																																																																												
	mm	NTS																																																																																																																																																																																																																																																																	
GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 757367 DRWN: SOKUMURA01 2023/07/21 CHK'D: SAKIYAMA 2023/09/12 APPR: AIDA 2023/09/12 INITIAL REVISION: DRWN: RWATANABE01 2017/09/15 APPR: TKANEKO 2017/09/26				MICRO-LOCK PLUS 1.25 W/B SINGLE ROW RECEPTACLE HOUSING LOW-HALOGEN																																																																																																																																																																																																																																																												
ANGULAR TOL	±	3.0°					PRODUCT CUSTOMER DRAWING																																																																																																																																																																																																																																																												
4 PLACES	±	0.2					DOCUMENT NUMBER																																																																																																																																																																																																																																																												
3 PLACES	±	0.2					2045320000-SD																																																																																																																																																																																																																																																												
2 PLACES	±	0.2					DOC TYPE	DOC PART	REVISION																																																																																																																																																																																																																																																										
1 PLACE	±	0.2					PSD	000	G																																																																																																																																																																																																																																																										
0 PLACES	±	0.2																																																																																																																																																																																																																																																																	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER		SHEET NUMBER																																																																																																																																																																																																																																																										
				A3-SIZE	204532	SEE CHART	GENERAL		3 OF 3																																																																																																																																																																																																																																																										
A																																																																																																																																																																																																																																																																			
B																																																																																																																																																																																																																																																																			
C																																																																																																																																																																																																																																																																			
D																																																																																																																																																																																																																																																																			
E																																																																																																																																																																																																																																																																			
F																																																																																																																																																																																																																																																																			