

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301510021](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Adapter Non-NEMA Receptacle - Female End, 20A/250V, NEMA 5-15 Plug - Male End, 20A/250V

**Documents:**  
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

|                               |                                                      |
|-------------------------------|------------------------------------------------------|
| <b>Agency Certification</b>   |                                                      |
| CSA                           | LR6837                                               |
| <b>General</b>                |                                                      |
| Product Family                | Wiring Devices                                       |
| Series                        | <a href="#">130151</a>                               |
| IP Rating                     | N/A                                                  |
| NEMA Configuration            | NEMA 5-15                                            |
| Overview                      | <a href="#">Heavy-Duty Industrial Wiring Devices</a> |
| Product Name                  | Super-Safeway                                        |
| Receptacle Type               | N/A                                                  |
| Specialty                     | N/A                                                  |
| Type                          | Adapter                                              |
| UPC                           | 78678875022                                          |
| <b>Physical</b>               |                                                      |
| Flange                        | No                                                   |
| Flip Lid                      | No                                                   |
| Gender                        | Male                                                 |
| Length                        | N/A                                                  |
| Locking Blade                 | No                                                   |
| Poles                         | 2-pole/3-wire                                        |
| <b>Electrical</b>             |                                                      |
| Cord Type                     | N/A                                                  |
| Current - Maximum per Contact | 20.0A                                                |
| GFCI                          | No                                                   |
| Lighted Connector             | No                                                   |
| Voltage - Maximum             | 250V                                                 |
| <b>Material Info</b>          |                                                      |
| Engineering Number            | 1732                                                 |



Series image - Reference only

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b>                                                 |                   |
| <b>Not Reviewed</b>                                           |                   |
| <b>EU RoHS</b>                                                | <b>China RoHS</b> |
| <b>Not Reviewed</b>                                           |                   |
| <b>REACH SVHC</b>                                             |                   |
| Not Reviewed                                                  |                   |
| <b>Halogen-Free</b>                                           |                   |
| <b>Status</b>                                                 |                   |
| <b>Not Reviewed</b>                                           |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Reviewed      |
| ELV                                                           | Not Reviewed      |
| RoHS Phthalates                                               | Not Reviewed      |

**Search Parts in this Series**  
[130151](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301510021](#)