

# PSBJ-URTK 6 RD - Test plug strip

3026719

<https://www.phoenixcontact.com/us/products/3026719>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug strip, number of positions: 1, color: red

## Your advantages

- The test socket PSBJ... is used in place of the normal bridge screw and ensures the voltage pick-off on a bridged group of terminals
- The test sockets are tailored to the special applications encountered in the power supply industry

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 3026719             |
| Packing unit                         | 10 pc               |
| Minimum order quantity               | 10 pc               |
| Sales key                            | BE19                |
| Product key                          | BE1Z3X              |
| Catalog page                         | Page 587 (C-1-2019) |
| GTIN                                 | 4017918453763       |
| Weight per piece (including packing) | 2.47 g              |
| Weight per piece (excluding packing) | 2.435 g             |
| Customs tariff number                | 85366990            |
| Country of origin                    | PL                  |

# PSBJ-URTK 6 RD - Test plug strip

3026719

<https://www.phoenixcontact.com/us/products/3026719>



## Technical data

### Product properties

|                     |             |
|---------------------|-------------|
| Product type        | Test socket |
| Number of positions | 1           |


### Data management status

|                  |    |
|------------------|----|
| Article revision | 06 |
|------------------|----|

### Connection data

|                   |                  |
|-------------------|------------------|
| Connection method | Screw connection |
|-------------------|------------------|

### Dimensions

|                     |                                                                                     |
|---------------------|-------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 6 mm                                                                                |
| Height              | 6 mm                                                                                |
| Depth on NS 35/7,5  | 15 mm                                                                               |
| Pin diameter        | 4.1 mm                                                                              |

### Material specifications

|                     |                |
|---------------------|----------------|
| Color               | red (RAL 3001) |
| Material            | Brass          |
| Insulating material | PA             |


# PSBJ-URTK 6 RD - Test plug strip

3026719

<https://www.phoenixcontact.com/us/products/3026719>



## Drawings



# PSBJ-URTK 6 RD - Test plug strip



3026719

<https://www.phoenixcontact.com/us/products/3026719>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27440313 |
| ECLASS-13.0 | 27440313 |
| ECLASS-12.0 | 27440313 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002255 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 20122000 |
|-------------|----------|

# PSBJ-URTK 6 RD - Test plug strip



3026719  
<https://www.phoenixcontact.com/us/products/3026719>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)