

PZ/2 - Strain relief



3040627

<https://www.phoenixcontact.com/us/products/3040627>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Strain relief, width: 9.3 mm, height: 48.7 mm, number of positions: 2, color: black

Your advantages

- The conductor can be fixed using Phoenix Contact cable binders
- Strain relief can be snapped onto the outside of the plug as an option

Commercial data

Item number	3040627
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE02
Product key	BE214Z
Catalog page	Page 362 (C-1-2019)
GTIN	4017918832766
Weight per piece (including packing)	1.14 g
Weight per piece (excluding packing)	1.14 g
Customs tariff number	39269097
Country of origin	PL

PZ/2 - Strain relief

3040627

<https://www.phoenixcontact.com/us/products/3040627>



Technical data

Product properties

Product type	Strain relief
Number of positions	2

Data management status

Article revision	01
------------------	----

Dimensions

Width	9.3 mm
Height	48.7 mm

Material specifications

Color	black (RAL 9005)
Material	PA-GF
Flammability rating according to UL 94	V0

PZ/2 - Strain relief

3040627

<https://www.phoenixcontact.com/us/products/3040627>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3040627>



EAC

Approval ID: RU C-DE.BL08.B.00644

PZ/2 - Strain relief

3040627

<https://www.phoenixcontact.com/us/products/3040627>



Classifications

ECLASS

ECLASS-11.0	27141192
ECLASS-13.0	27250192
ECLASS-12.0	27141192

ETIM

ETIM 9.0	EC002848
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PZ/2 - Strain relief

3040627

<https://www.phoenixcontact.com/us/products/3040627>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com