

N Female Connector Solder Attachment 2 Hole Flange Mount Pin Terminal, 1.0 inch Hole Spacing

PE44079



Configuration

- N Female Connector
- MIL-STD-348
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: Pin
- 2 Hole Flange

Features

- Silver Plated Contact
- Contact plating according to QQ-S-365

Applications

- General Purpose Test
- Rack and Panel Mount Applications

Description

Pasternack's PE44079 type N , N, Standard, connector with solder attachment Pin terminal is part of our full line of RF components available for same-day shipping. This type N 2 hole flange connector allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Our type N female 2 hole flange connector PE44079 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Impedance		50		Ohms

Mechanical Specifications

Size

Length	1.441 in [36.6 mm]
Width	0.64 in [16.26 mm]
Height	1.3 in [33.02 mm]
Weight	0.0572 lbs [25.95 g]

Material Specifications

Description	Material	Plating
Contact		Silver QQ-S-365
Insulation	PTFE	
Body	Brass	Nickel QQ-N-290

N Female Connector Solder Attachment 2 Hole Flange Mount Pin Terminal, 1.0 inch Hole Spacing

PE44079



Environmental Specifications

Temperature

Operating Range

-65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

N Female Connector Solder Attachment 2 Hole Flange Mount Pin Terminal, 1.0 inch Hole Spacing from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Female Connector Solder Attachment 2 Hole Flange Mount Pin Terminal, 1.0 inch Hole Spacing PE44079](#)

URL: <https://www.pasternack.com/n-female-standard-pin-terminal-connector-pe44079-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE44079 CAD Drawing

N Female Connector Solder Attachment 2 Hole Flange Mount Pin Terminal, 1.0 inch Hole Spacing

