

RZ 2,5-DMKDS - Pitch spacer



1740042

<https://www.phoenixcontact.com/us/products/1740042>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pitch spacer, increases the pitch by 2.5 mm, interlocks with terminal block of the same shape

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1740042 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | AA18 |
| Product key | AARZCA |
| GTIN | 4017918028206 |
| Weight per piece (including packing) | 0.542 g |
| Weight per piece (excluding packing) | 0.51 g |
| Customs tariff number | 85389099 |
| Country of origin | PL |

RZ 2,5-DMKDS - Pitch spacer



1740042

<https://www.phoenixcontact.com/us/products/1740042>

Technical data

Product properties

| | |
|---------------------|------------------|
| Product type | Pitch spacer |
| Product family | DECKEL + RZ + DP |
| Number of positions | 1 |
| Pitch | 0 mm |

Data management status

| | |
|------------------|----|
| Article revision | 00 |
|------------------|----|

Material specifications

| | |
|--|------------------|
| Color (Housing) | green (RAL 6021) |
| Flammability rating according to UL 94 | V0 |

Dimensions

| | |
|------------------|----------|
| Width | 2.5 mm |
| Installed height | 20 mm |
| Height | 20 mm |
| Length | 27.78 mm |
| Pitch | 0 mm |

RZ 2,5-DMKDS - Pitch spacer



1740042

<https://www.phoenixcontact.com/us/products/1740042>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-12.0 | 27460407 |
| ECLASS-11.0 | 27460407 |
| ECLASS-13.0 | 27460407 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002943 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

RZ 2,5-DMKDS - Pitch spacer

1740042

<https://www.phoenixcontact.com/us/products/1740042>



Environmental product compliance

| | |
|---|--|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com