

PSB 3/10/4 - Test plug strip



0601292

<https://www.phoenixcontact.com/us/products/0601292>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug strip, number of positions: 1, color: silver

Your advantages

- Test sockets PSB ... are used for a reliable test pick-off
- With PSB 6/5/6, the test plug with a 4 mm diameter is used
- All test sockets are screwed into the bridge shaft

Commercial data

Item number	0601292
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z3X
Catalog page	Page 590 (C-1-2019)
GTIN	4017918003012
Weight per piece (including packing)	0.965 g
Weight per piece (excluding packing)	0.965 g
Customs tariff number	85366990
Country of origin	PL

PSB 3/10/4 - Test plug strip

0601292

<https://www.phoenixcontact.com/us/products/0601292>



Technical data

Product properties

Product type	Test socket
Number of positions	1


Data management status

Article revision	04
------------------	----

Connection data

Test socket torque	M3
Connection method	Plug-in connection

Dimensions

Dimensional drawing	
Width	4 mm
Height	10 mm
Pin diameter	2.4 mm
Screw thread	M3

Material specifications

Color	silver-colored
Contact material	Silver-plated brass

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

Mounting

Screw thread	M3
--------------	----


PSB 3/10/4 - Test plug strip

0601292

<https://www.phoenixcontact.com/us/products/0601292>



Drawings



PSB 3/10/4 - Test plug strip

0601292

<https://www.phoenixcontact.com/us/products/0601292>



Classifications

ECLASS

ECLASS-11.0	27440313
ECLASS-12.0	27440313
ECLASS-13.0	27440313

ETIM

ETIM 9.0	EC002255
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

PSB 3/10/4 - Test plug strip



0601292
<https://www.phoenixcontact.com/us/products/0601292>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com