


# DF-PTMC-3-ZB - Marker adapter



3270405

<https://www.phoenixcontact.com/us/products/3270405>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker adapter, for accommodating the marking, depth: 13 mm, width: 12.2 mm, height: 30 mm, color: gray

## Your advantages

- For lateral latching on to PTMC
- Accessories for snapping on to PTMC
- Enables the creation of a marking matrix
- Easy marking options

## Commercial data

Item number	3270405
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE69
Product key	BE6ZWX
Catalog page	Page 57 (C-1-2019)
GTIN	4055626314945
Weight per piece (including packing)	2.74 g
Weight per piece (excluding packing)	2.51 g
Customs tariff number	39269097
Country of origin	PL

# DF-PTMC-3-ZB - Marker adapter

3270405

<https://www.phoenixcontact.com/us/products/3270405>



## Technical data

### Product properties

Product type	Mounting material
Data management status	
Article revision	00

### Dimensions

Width	12.2 mm
Height	30 mm
Depth	13 mm

### Material specifications

Color	gray (RAL 7042)
Material	PA

### Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# DF-PTMC-3-ZB - Marker adapter



3270405

<https://www.phoenixcontact.com/us/products/3270405>

## Classifications

### ECLASS

ECLASS-11.0	27141190
ECLASS-12.0	27141190
ECLASS-13.0	27141190

### ETIM

ETIM 9.0	EC002848
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# DF-PTMC-3-ZB - Marker adapter



3270405

<https://www.phoenixcontact.com/us/products/3270405>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)