


A PERFECT ALLIANCE.

# ODU AMC<sup>®</sup> SERIES T ACCESSORIES

## Protective Caps:

Part	Material	plating
Cap	Aluminium	Tin-nickel over electroless nickel
Crimp ferrule	Brass	Black zinc-nickel over nickel
Lanyard	Black aramid	
Cable lug	Copper	Black zinc-nickel

Material number	ODU number	Shell Size	Type
50271659	7TE.197.001.661.000	9	G8 / G6 / GB / K1 / KB
50271669	7TE.597.001.661.00A	9	C1 / CB A-coding
50300753	7TE.597.001.661.00C	9	C1 / CB C-coding
50271693	7TE.297.001.661.000	9	S1 / SB A1 / AB
50272233	7TH.197.001.661.000	12	G8 / G6 / GB / K1 / KB
50273452	7TH.597.001.661.00A	12	C1 / CB A-coding
50300741	7TH.597.001.661.00C	12	C1 / CB C-coding
50273453	7TH.297.001.661.000	12	S1 / SB A1 / AB



A PERFECT ALLIANCE.

# ODU AMC<sup>®</sup> SERIES T ACCESSORIES

## Sealing Plugs:

Material	
PPSU	Polyphenyl sulfone

Contact size	Material number	ODU number	MIL-No.	color
#16	50289878	021.315.951.937.000	MS27488-16-2	green
#20	50289883	021.315.901.937.000	MS27488-20-2	red
#20MD	50292731	021.315.949.937.000	-	orange
#22D	50289889	021.315.942.937.000	MS27488-22-2	black
#22MD	50292732	021.315.948.937.000	-	green
#26	50292733	021.315.941.937.000	-	red



A PERFECT ALLIANCE.


# ODU AMC<sup>®</sup> SERIES T ACCESSORIES

## Backshells

Suitable for the following connector types **CB / SB / AB / GB / KB**

Material	Plating
Aluminium	Nickel

Type	Shell size	MIL-Standard No.	Material No.	ODU No.
Straight	9	M85049/38S9N	50298708	921-000.006.000.290
Straight	12	M85049/38S13N	50298723	921.000.006.000.296
Straight	9	M85049/88-9N03	50298717	921.000.006.000.292
Straight	12	M85049/88-13N03	50298725	921.000.006.000.298
Right angled	9	M85049/90-9N03	50298718	921.000.006.000.293
Right angled	12	M85049/90-13N03	50298726	921.000.006.000.299
Straight	9	M85049/189N02	50298719	921.000.006.000.294
Straight	12	M85049/1813N02	50298818	921.000.006.000.402
Straight	12	M85049/1813N03	50298823	921.000.006.000.403
Straight	12	M85049/1813N04	50298845	921.000.006.000.404



A PERFECT ALLIANCE.

# ODU AMC<sup>®</sup> SERIES T ACCESSORIES

## Crimp Sleeve

Material	Plating
CuTeP	Nickel

Shell Size	Material number	ODU number	Style
9	50269982	7TE.440.101.304.000	1
9	50291239	7TE.440.101.304.001	2
12	50270266	7TH.440.101.304.000	1
12	50291232	7TH.440.101.304.001	2

## Tie-Dex Micro Bands for Band IT Solution

Shell Size	Material number	ODU number
all	50156242	921.000.004.000.248

## Heat-Shrink parts

Heatshrinkable straight				
ShellSize	Material number	ODU number	Hellermann	TE Connectivity
all	50157036	921.000.010.008.084	401-52880	202D121-3-60

Heatshrinkable right angled			
Shell Size	Material number	ODU number	Hellermann
all	50157039	921.000.010.008.087	411-52480

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## ODU:

[7TE.197.001.661.000](#) [7TE.297.001.661.000](#) [7TE.440.101.304.000](#) [7TE.440.101.304.001](#) [7TE.597.001.661.000](#)  
[7TH.197.001.661.000](#) [7TH.297.001.661.000](#) [7TH.440.101.304.000](#) [7TH.440.101.304.001](#) [7TH.597.001.661.000](#)  
[7TE.597.001.661.00A](#) [7TH.597.001.661.00A](#) [7TE-597-001-661-00A](#) [7TE-197-001-661-000](#) [7TE-297-001-661-000](#)  
[7TE-440-101-304-000](#) [7TE-440-101-304-001](#) [7TH-197-001-661-000](#) [7TH-297-001-661-000](#) [7TH-440-101-304-000](#)  
[7TH-440-101-304-001](#) [7TH-597-001-661-00A](#)