

MPS-MT/ 4MM - Test plug

3048577

<https://www.phoenixcontact.com/us/products/3048577>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, with solder connection up to 1 mm² conductor cross section, number of positions: 1, color: silver

Your advantages

- The test plug makes contact in all test sockets with a 4 mm diameter
- Two-piece test plug for individual plug color combinations

Commercial data

Item number	3048577
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BE19
Product key	BE1Z3X
Catalog page	Page 410 (C-1-2019)
GTIN	4046356072779
Weight per piece (including packing)	2.09 g
Weight per piece (excluding packing)	1.94 g
Customs tariff number	85366990
Country of origin	DE

MPS-MT/ 4MM - Test plug

3048577

<https://www.phoenixcontact.com/us/products/3048577>



Technical data

Product properties

Product type	Test plug terminal block
Number of positions	1

Data management status

Article revision	02
------------------	----

Electrical properties

Nominal voltage U_N	60 V DC (30 V AC)
Nominal current I_N	16 A

Connection data

Connection method	Solder connection
-------------------	-------------------

Dimensions

Height	26 mm
Length contact range	8.4 mm
Pin diameter	4.4 mm
Note on dimensions	Length without insulating sleeve

Material specifications

Color	silver-colored
-------	----------------

MPS-MT/ 4MM - Test plug

3048577

<https://www.phoenixcontact.com/us/products/3048577>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3048577>



EAC

Approval ID: RU C-DE.BL08.B.00511

MPS-MT/ 4MM - Test plug



3048577

<https://www.phoenixcontact.com/us/products/3048577>

Classifications

ECLASS

ECLASS-11.0	27440313
ECLASS-12.0	27440313
ECLASS-13.0	27440313

ETIM

ETIM 9.0	EC002255
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

MPS-MT/ 4MM - Test plug



3048577
<https://www.phoenixcontact.com/us/products/3048577>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com