


PS-UK 2,5 B/Z-6 - Test plug

3001239

<https://www.phoenixcontact.com/us/products/3001239>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, number of positions: 1, color: red

Your advantages

- The test plug reliably makes contact in the bridge shaft and in all test sockets with a 2.3 mm or 4 mm diameter
- Individual test adapters can be combined using the modular PS-...2,3MM test plug.

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 3001239 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BE19 |
| Product key | BE1Z3X |
| Catalog page | Page 410 (C-1-2019) |
| GTIN | 4017918089856 |
| Weight per piece (including packing) | 51.7 g |
| Weight per piece (excluding packing) | 50 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

PS-UK 2,5 B/Z-6 - Test plug

3001239

<https://www.phoenixcontact.com/us/products/3001239>



Technical data

Product properties

| | |
|---------------------|--------------------------|
| Product type | Test plug terminal block |
| Number of positions | 1 |
| Pitch | 6.2 mm |

Connection data

| | |
|-------------------|------------------------|
| Connection method | Spring-cage connection |
|-------------------|------------------------|

Dimensions

| | |
|---------------------|--------|
| Dimensional drawing | |
| Width | 5 mm |
| Pin diameter | 6.5 mm |
| Pitch | 6.2 mm |

Material specifications

| | |
|--|-----|
| Color | red |
| Material | PA |
| Flammability rating according to UL 94 | V2 |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 115 °C |
|---------------------------------|-------------------|

PS-UK 2,5 B/Z-6 - Test plug


3001239

<https://www.phoenixcontact.com/us/products/3001239>



Drawings

Dimensional drawing



PS-UK 2,5 B/Z-6 - Test plug

3001239

<https://www.phoenixcontact.com/us/products/3001239>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27440313 |
|-------------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121410 |
|-------------|----------|

Environmental product compliance

| | |
|---|---|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |