

D-MBK 5/E-T - End cover

1413706

<https://www.phoenixcontact.com/us/products/1413706>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, width: 1 mm, height: 30.3 mm, color: gray



Commercial data

Item number	1413706
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE19
Product key	BE1Z1X
Catalog page	Page 506 (C-1-2019)
GTIN	4017918021252
Weight per piece (including packing)	0.938 g
Weight per piece (excluding packing)	0.92 g
Customs tariff number	85389099
Country of origin	DE

D-MBK 5/E-T - End cover

1413706

<https://www.phoenixcontact.com/us/products/1413706>



Technical data

Product properties

Product type	End cover
Data management status	
Article revision	01

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V2

Dimensions

Width	1 mm
Height	30.3 mm

D-MBK 5/E-T - End cover



1413706

<https://www.phoenixcontact.com/us/products/1413706>

Classifications

ECLASS

ECLASS-11.0	27141133
-------------	----------

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

D-MBK 5/E-T - End cover



1413706
<https://www.phoenixcontact.com/us/products/1413706>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com