

FBP-3/15 TR - Cover profile

3069994

<https://www.phoenixcontact.com/us/products/3069994>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover profile, can optionally be sealed, depth: 32 mm, width: 74.1 mm, height: 154.9 mm, color: transparent

Commercial data

Item number	3069994
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE06
Product key	BE6113
GTIN	4055626398822
Weight per piece (including packing)	93.3 g
Weight per piece (excluding packing)	91 g
Customs tariff number	39162000
Country of origin	PL

FBP-3/15 TR - Cover profile

3069994

<https://www.phoenixcontact.com/us/products/3069994>



Technical data

Product properties

Product type	Cover profile
Insulation characteristics	
Overvoltage category	III

Dimensions

Width	74.1 mm
Height	154.9 mm
Depth	32 mm

Material specifications

Color	transparent
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PVC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

FBP-3/15 TR - Cover profile

3069994

<https://www.phoenixcontact.com/us/products/3069994>



Classifications

ECLASS

ECLASS-11.0	27141190
ECLASS-13.0	27141190
ECLASS-12.0	27141190

ETIM

ETIM 9.0	EC002848
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBP-3/15 TR - Cover profile

3069994

<https://www.phoenixcontact.com/us/products/3069994>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com