

DP PS-6 - Spacer plate

3036738

<https://www.phoenixcontact.com/us/products/3036738>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Spacer plate, depth: 29 mm, width: 6.2 mm, height: 22.4 mm, number of positions: 1, color: red

Commercial data

Item number	3036738
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
Catalog page	Page 98 (C-1-2019)
GTIN	4017918818982
Weight per piece (including packing)	1.752 g
Weight per piece (excluding packing)	1.5 g
Customs tariff number	39269097
Country of origin	PL

DP PS-6 - Spacer plate

3036738

<https://www.phoenixcontact.com/us/products/3036738>



Technical data

Product properties

Product type	Partition plate
Number of positions	1

Data management status

Article revision	01
------------------	----

Material specifications

Color	red (RAL 3001)
Material	PA
Flammability rating according to UL 94	V0

Dimensions

Dimensional drawing	
Width	6.2 mm
Height	22.4 mm
Depth	29 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, no longer than 24 h, -60°C to +70°C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C ()
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

DP PS-6 - Spacer plate


3036738

<https://www.phoenixcontact.com/us/products/3036738>



Drawings

Dimensional drawing



DP PS-6 - Spacer plate



3036738

<https://www.phoenixcontact.com/us/products/3036738>

Classifications

ECLASS

ECLASS-11.0	27141133
ECLASS-12.0	27141133
ECLASS-13.0	27250301

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

DP PS-6 - Spacer plate



3036738
<https://www.phoenixcontact.com/us/products/3036738>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com