



Find blown fuses fast with *easyID*™



New in 2019
easyID ATR
illuminating fuses

Product description:

Bussmann™ series *easyID* illuminating blade fuses and holders use Light Emitting Diode (LED) technology to indicate that a fuse has opened, making it easy to spot in fuse panels tucked under dark dashboards.

Illuminating blade fuses are the ideal choice for fast and easy fuse replacement. Popular fuse types (ATR, ATC, ATM, Maxi™, FMX) are available in common fuse ratings for consumer convenience.

ATR fuses are the latest space-saving fuses for newer vehicles, while ATC fuses are used in both new and older automobiles and light trucks.

ATM fuses are used for a wide variety of applications involving late-model OEM vehicles.

Maxi fuses are used for protecting circuits in wiring harnesses (usually found under the hood in a fuse panel near the battery) and are increasingly used in domestic cars and some imports.

Female Maxi (FMX) fuses are used for late-model vehicles and are available in the most popular amp ratings.

Features and benefits:

- Available in popular sizes and ratings to cover the most common replacement fuse needs.
- Illuminating fuse holders use regular ATM and ATC blade fuses.
- Universal color coding makes it easier to match with a traditional non-illuminating fuse.
- Value packs, assortment and service kits provide popular packaging options to maximize retail sales.
- Specialty (black) packaging helps fuses stand out in any retail setting as being the superior choice.

easyID Illuminating single-amp retail packs

Catalog number	Amp	Color	UPC	Unit pack		Shelf carton		Master carton	
				Qty.	Dimensions (HxWxD)	Qty.	Dimensions (LxWxH)	Qty.	Dimensions (LxWxH)
BP/ATR-10ID	10	Red	051712742283	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATR-15ID	15	Blue	051712742290	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATR-20ID	20	Yellow	051712742306	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATR-30ID	30	Green	051712742313	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATC-3ID	3	Violet	051712237796	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATC-5ID	5	Tan	051712237819	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATC-7½ID	7½	Brown	051712237826	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATC-10ID	10	Red	051712237833	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATC-15ID	15	Blue	051712237840	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATC-20ID	20	Yellow	051712237857	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATC-25ID	25	Clear	051712237864	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATC-30ID	30	Green	051712237871	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATC-35ID	35	Blue-Green	051712237888	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATC-40ID	30	Orange	051712237895	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATM-3ID	3	Violet	051712237901	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATM-5ID	5	Tan	051712237925	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATM-7½ID	7½	Brown	051712237932	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATM-10ID	10	Red	051712237949	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATM-15ID	15	Blue	051712237956	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATM-20ID	20	Yellow	051712237963	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATM-25ID	25	Clear	051712237970	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/ATM-30ID	30	Green	051712237987	2	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/MAX-20ID	20	Yellow	051712237994	1	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/MAX-30ID	30	Green	051712238007	1	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/MAX-40ID	40	Orange	051712238014	1	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/MAX-50ID	50	Red	051712238021	1	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/MAX-60ID	60	Blue	051712238038	1	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/MAX-70ID	70	Tan	051712238045	1	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/MAX-80ID	80	Natural	051712238052	1	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/MAX-100ID	100	Violet	051712238991	1	3.72" x 1.77" x 0.58"	5	3.82" x 1.88" x 2.88"	120	12.00" x 12.00" x 4.13"
BP/FMX-20ID	20	Blue	051712283731	1	3.72" x 1.77" x 0.58"	5	2.88" x 1.88" x 3.82"	120	12.00" x 12.00" x 4.13"
BP/FMX-30ID	30	Pink	051712283748	1	3.72" x 1.77" x 0.58"	5	2.88" x 1.88" x 3.82"	120	12.00" x 12.00" x 4.13"
BP/FMX-40ID	40	Green	051712283755	1	3.72" x 1.77" x 0.58"	5	2.88" x 1.88" x 3.82"	120	12.00" x 12.00" x 4.13"
BP/FMX-50ID	50	Red	051712283762	1	3.72" x 1.77" x 0.58"	5	2.88" x 1.88" x 3.82"	120	12.00" x 12.00" x 4.13"
BP/FMX-60ID	60	Yellow	051712283779	1	3.72" x 1.77" x 0.58"	5	2.88" x 1.88" x 3.82"	120	12.00" x 12.00" x 4.13"

easyID Illuminating assortment retail packs

Catalog number	Description	Contents	UPC
BP/ATR-AID	ATR fuse assortment	(1) ATR-10, (1) ATR-15, (2) ATR-20, (1) ATR-30	051712742276
BP/ATC-AID	ATC fuse assortment	(1) ATC-10, (1) ATC-15, (1) ATC-20, (1) ATC-25, (1) ATC-30	051712238205
ATC-ID-SK	ATC fuse service kit	(6) ATC-5, (6) ATC-10, (6) ATC-15, (6) ATC-20, (6) ATC-25, (6) ATC-30	051712238229
BP/ATM-AID	ATM fuse assortment	(1) ATM-5 (1) ATM-10, (1) ATM-15, (1) ATM-20, (1) ATM-25, (1) ATC-30	051712238212
ATM-ID-SK	ATM fuse service kit	(6) ATM-5, (6) ATM-10, (6) ATM-15, (6) ATM-20, (6) ATM-25, (6) ATM-30	051712238236

easyID Illuminating holders for blade fuses

Catalog number	Max volts/amps	Lead-wire	UPC
ATM-FHID	32 V/20 A	#16	051712238083
ATC-FHID	32 V/20 A	#16	051712238069
MAX-FHID	32 V/20 A	#6	051712514545



For Eaton's Bussmann series product information, call 1-855-287-7626 or visit: Eaton.com/BussmannConsumer

Follow us on social media to get the latest product and support information.



Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

Bussmann Division
114 Old State Road
Ellisville, MO 63021
United States
Eaton.com/bussmannseries

Eaton, Bussmann, *easyID* and Maxi are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

© 2018 Eaton
All Rights Reserved
Printed in USA
Publication No. 5085
October 2018

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[ATC-FHID](#) [ATC-ID-SK](#) [ATM-FHID](#) [ATM-ID-SK](#) [BK/ATM-10ID](#) [BK/ATM-20ID](#) [VP/ATM-20ID](#) [VP/ATC-25ID](#)
[BP/ATM-20ID](#) [BP/ATM-3ID](#) [BP/ATC-5ID](#) [VP/ATC-10ID](#) [BK/ATC-30ID](#) [BP/ATC-15ID](#) [VP/ATM-15ID](#) [VP/ATM-30ID](#)
[BP/ATM-25ID](#) [BP/ATM-10ID](#) [BP/ATC-25ID](#) [BP/ATC-40ID](#) [BP/ATC-30ID](#) [BK/ATM-15ID](#) [BK/ATM-30ID](#) [BP/ATM-5ID](#)
[BP/ATC-10ID](#) [BK/ATC-25ID](#) [VP/ATM-25ID](#) [BK/ATM-25ID](#) [BP/ATC-7-1/2ID](#) [BP/ATC-3ID](#) [VP/ATC-20ID](#) [BP/ATC-20ID](#)
[BP/ATM-7-1/2ID](#) [BP/ATC-35ID](#) [VP/ATC-30ID](#) [BP/ATM-15ID](#) [BP/ATM-30ID](#) [VP/ATC-15ID](#) [VP/ATM-10ID](#) [BP/MAX-](#)
[100ID](#) [BP/MAX-30ID](#) [BP/MAX-20ID](#) [BP/MAX-40ID](#) [BP/MAX-50ID](#) [BP/MAX-70ID](#) [BP/MAX-60ID](#) [BP/MAX-80ID](#)
[BK/ATC-3ID](#) [BP/ATC-AID](#) [BK/ATC-7-1/2ID](#) [BK/ATC-5ID](#) [BK/ATM-7-1/2ID](#) [BK/ATM-5ID](#) [BP/ATM-AID](#) [FP-ATM-06ID](#)
[FP-ATM-10ID](#) [FP-ATC-04ID](#) [FP-ATC-06ID](#) [FP-ATC-10ID](#) [FP-ATM-04ID](#) [BK/MAX-80ID](#) [BK/MAX-60ID](#) [BP/FMX-](#)
[50ID](#) [BK/MAX-50ID](#) [BK/MAX-30ID](#) [BK/MAX-40ID](#) [BP/FMX-20ID](#) [BP/FMX-30ID](#) [BP/FMX-40ID](#) [MAX-FHID](#)