

General Information

Extended Product Type:	PG5-R1
Product ID:	1SNK900402R0000
EAN:	3472599097346
Catalog Description:	PG5-R1 Disconnect Plug - Orange
Long Description:	Allow disconnect function when associated with the disconnect with plug terminal blocks.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Component Plugs

Ordering

Minimum Order Quantity:	20 piece
Customs Tariff Number:	85369010
Color:	Orange

Dimensions

Product Net Height:	31 mm
Product Net Length:	39 mm
Product Net Depth:	39 mm
Product Net Weight:	3.5 g
Product Net Width:	5.2 mm

Technical

Spacing:	5.2 mm
Function:	Disconnect Plugs
Rated Current (I_n):	Main Circuit 18 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 480 A
Rated Voltage (U_r):	400 V
Rated Impulse Withstand Voltage (U_{imp}):	6000 V
Dielectric Test Voltage:	1890 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	ZK2.5-SP ZK2.5-SP-4P ZP2.5-SP ZS10-S ZS10-SP ZS4-SP ZS4-SP-R1 ZS4-SP-T2 ZS4-SP-T2-R1

Technical UL/CSA

Flammability According to UL94:	V0
Maximum Operating Voltage UL/CSA:	Main Circuit 150 V

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
Data Sheet, Technical Information:	1SNK160037D0201
RoHS Information:	1SND230501F0202

Classifications

E-nummer:	2925158
ETIM 4:	EC002018 - Component plug terminal block
ETIM 5:	EC002018 - Component plug terminal block
ETIM 6:	EC002018 - Component plug terminal block
Object Classification Code:	X

Container Information

Package Level 1 Width:	170 mm
Package Level 1 Length:	125 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.07 kg
Package Level 1 EAN:	3472599097346
Package Level 2 Units:	2000 piece
Package Level 2 Width:	200 mm
Package Level 2 Length:	300 mm
Package Level 2 Height:	200 mm
Package Level 3 Units:	192000 piece
Product Packing Type:	Bag
Package Level 1 Units:	20 piece

