

Boeing BACC63

How to Order

HOW TO ORDER - BOEING BACC63 CT & CU

1.	2.	3.	4.	5.	6.	7.	8.
Boeing Basic Number	Style	Shell Size	Shell Finish & Contact	Insert Arrangement	Contact Type	Alternate Keying Position	Ordering Option
BACC63	CT	15	—	19	P	N	H

COMPOSITE

1. BOEING NUMBER
BACC63 Boeing

2. STYLE
CT Composite Plug
CU Composite Receptacle

3. SHELL SIZE
15 One Shell Size

4. SHELL FINISH & CONTACT
C CT Style Only. Cadmium Plated, Grounded
D Cadmium Plated, ungrounded
G Nickel Plated, Grounded
— Nickel Plated, Ungrounded

5. INSERT ARRANGEMENTS-
Consult Amphenol Aerospace for insert arrangements available.

6. CONTACT TYPE
P Pin
S Socket

7. ALTERNATE KEYING POSITION
N Normal
A-E Alternates

8. ORDERING OPTIONS
H Without Contacts & Seal Plugs
Blank With Contacts & Seal Plugs

HOW TO ORDER - BOEING BACC63 DB & DC

1.	2.	3.	4.	5.	6.
Boeing Basic Number	Style	Shell Size-Insert Arrangement	Contact Type	Alternate Keying Position	Ordering Option
BACC63	DB	15-19	P	N	H
BACC63	DC	17-8	P	N	H

STAINLESS STEEL

1. BOEING NUMBER
BACC63 Boeing

2. SELECT A STYLE
DB Stainless Steel Plug
DC Stainless Steel Receptacle

4. CONTACT TYPE
P Pin
S Socket

5. ALTERNATE KEYING POSITION
N Normal
A-E Alternates

6. ORDERING OPTION
H Without Contacts & Seal Plugs
Blank With Contacts & Seal Plugs

3. SELECT A SHELL SIZE & INSERT ARRANGEMENT SEE PAGES 2-5

Shell Size & Insert Arrangements are on pages 2-5. First number represents Shell Size, second number is the Insert Arrangement. Please include the dash.

38999

III
Dualok
II
I
SJT
Access
Aquacon

Series III

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10-660977-46N](#) [BACC63CU25-8SEH](#) [BACC63CU25-8SCH](#) [BACC63CT25-8PNH](#) [BACC63CT25-8PEH](#)
[BACC63CT25-19SN](#) [BACC63CT25-8PDH](#) [BACC63CU25-8SDH](#) [BACC63CT25-8PCH](#) [BACC63CU25-8SBH](#)
[BACC63CT25-8PAH](#) [BACC63CU25-8SAH](#) [BACC63CT25-8PBH](#) [BACC63CU21-75SNH](#) [BACC63CM1203SN](#)
[BACC63CT11-35SN](#) [BACC63CT25D8SNH](#) [BACC63CU25-20SA](#) [BACC63CU13-35PN](#) [BACC63CU13-35PA](#)
[BACC63CT17-82SNH](#) [BACC63CU19-32PN](#) [BACC63CU9-98PA](#) [BACC63CU9-98PN](#) [BACC63CT21-11SN](#)
[BACC63CT19D11SA](#) [257A559-6](#) [12292860-41](#) [12292860-20](#) [10-660977-45A](#) [12292860-32](#) [12292860-42](#) [257A559-](#)
[7](#) [BACC63CT21-16PC](#) [BACC63CT15D35SN](#) [BACC63CT21-35PN](#) [BACC63CT25D29SNH](#) [BACC63CU25-35SN](#)
[BACC63CT9-98PNH](#) [BACC63CU23-21SN](#) [BACC63DB15-5SN](#) [BACC63CT25-35SBH](#) [BACC63CT9-35SN](#)
[BACC63CT9-35PN](#) [BACC63CT13-98SN](#) [BACC63CU13-98SN](#) [BACC63CU13-98PN](#) [BACC63DC25-37PNH](#)
[BACC63CU25-20SN](#) [BACC63CT9-98SNH](#) [BACC63CT17-35PN](#) [BACC63CT15D19SNH](#) [BACC63CT25-35PN](#)
[BACC63CU11-35PD](#) [BACC63CT15-5SA](#) [BACC63CT9-35PA](#) [BACC63CU11-35PN](#) [BACC63CU9-35PA](#)
[BACC63CT17-26PN](#) [BACC63CU9-35SN](#) [BACC63CU25-8SNH](#) [BACC63DC25-37SN](#) [BACC63CT25-35SNH](#)
[BACC63CT15-19PA](#) [BACC63CU13-4PN](#) [BACC63CU15-19SA](#) [BACC63CU15-35PA](#) [BACC63CU15-5PN](#)
[BACC63CU21-75SCH](#) [BACC63CT15-19PN](#) [BACC63CU11-35SN](#) [BACC63CU21-16PN](#) [BACC63CT23-35PN](#)
[BACC63CU21-41PA](#) [BACC63CU15-19PN](#) [BACC63DC25-4PN](#) [BACC63CU13-4SN](#) [BACC63CT11D35SN](#)
[BACC63CU15-35SN](#) [BACC63DC17-26SNH](#) [BACC63CU15-5PA](#) [BACC63CT15-35PN](#) [BACC63CT15-19PB](#)
[BACC63CT9-35SA](#) [BACC63DB9-35PN](#) [BACC63CT15-35SNH](#) [BACC63CT25D35SN](#) [BACC63CT15-35SA](#)
[BACC63CT9-98SA](#) [BACC63CT11-35PN](#) [BACC63CU23-35SN](#) [BACC63DC25-37PN](#) [BACC63CU15-5SN](#)
[BACC63CT11-98SN](#) [BACC63CU13-35SN](#) [BACC63CU13-98PA](#) [BACC63DB9-35SN](#) [BACC63CT13-35PC](#)
[BACC63CU21-35SN](#) [BACC63CT21D35SN](#)