

Product: FX Brilliance OM4 LC Keyed ☑





# FX Brilliance OM4 LC Keyed Connector

# **Product Description**

FX Brilliance Universal OM4 LC Keyed Mechanical Connector

TIA 568.3-D (MM)

Intermateability Requirement Compliant with TIA/EIA-604-10A (FOCIS 10)

# **Technical Specifications**

# **Product Overview**

Environmental Space:	Indoor
Suitable Applications:	Indoor termination of fiber cables: Patch panels, Communication outlets, Fiber-to-the-desk, Distribution frames, Campus, Customer premise, Access network, Data Centers

# Construction

### Fiber Cable Construction



# **Mechanical Characteristics**

# **Mechanical Specifications**

Operating Temp Range	-40°C to +75°C
Storage Temp Range	-40°C to +60°C
Durability	500 cycles, less than 0.2 dB change, FOTP-2
Maximum Insertion Loss:	0.50 dB
Typical Insertion Loss:	0.20 dB
Minimum Reflectance @ 155	50nm: -30 dB
Termination Style:	Mechanical
Durabilities@Termination1:	500 cycles, less than 0.2 dB change, FC

# **Temperature Range**

_

# **Product Material**

## Materials

Description	Material	Color
Boot	Rubber	Black
Protective Ferrule Cap	Plastic	Opaque
Connector Body	Plastic	Erika Violet
Ferrule	Ceramic	

# **Standards**

TIA/EIA Compliance:	TIA 568-C.3
EU Directive 2011/65/EU (RoHS 2):	Yes

MII Order #39 (China RoHS):	EUP 50
Safety Listing:	ACA

### **Related Part Numbers**

Included Parts:	900 μm boot, protective ferrule cap
Related Parts:	FX Brilliance Precision Installation Kit, Boots for 2mm and 3mm Jacketed Fiber, 250µm to 900µm break out kits.

#### Variants

Item #	Color	Packaging	UPC
AX105236-B25	Aqua	25-Pack	611589106085
AX105231-B25	Black	25-Pack	611589106030
AX105233-B25	Blue	25-Pack	611589106054
AX105237-B25	Brown	25-Pack	611589106092
AX105229-B25	Green	25-Pack	611589106016
AX105232-B25	Orange	25-Pack	611589106047
AX105228-B25	Red	25-Pack	611589106009
AX105235-B25	Rose	25-Pack	611589106078
AX105238-B25	Slate	25-Pack	611589106108
AX105238-S1	Slate	1-Pack	611589105705
AX105234-B25	Violet	25-Pack	611589106061
AX105239-B25	White	25-Pack	611589106115
AX105230-B25	Yellow	25-Pack	611589106023

### **Product Notes**

Packaging:	Individually packaged in a sealed plastic bag. Twenty-five (25) connectors come in a dust and moisture resistant blister package.
Notes:	Refer to Installation Guide PX105234 for installation procedures. Fiber can be reterminated up to 5 times with the same connector.

### **History**

Update and Revision:	Revision Number: 0.50 Revision Date: 03-04-2023	

#### © 2023 Belden, Inc

#### All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.