

CUSTOMER PRINT

PART NUMBER: 8382-XPG-5XX


- NOTES:
1. ALL PARTS TO BE BULK PACKED
 2. CONTACTS TO BE INSERTED INTO CONNECTOR
 3. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHEN NOTED WITH TOLERANCE

ASSY P/N	GROMMET SIZE
8382-XPG-513	.148 GROMMET I.D. FOR CABLE OD .13-.15 [3.3-3.8mm]
8382-XPG-516	.176 GROMMET I.D. FOR CABLE OD .16-.18 [4.1-4.6mm]
8382-XPG-519	.206 GROMMET I.D. FOR CABLE OD .19-.21 [4.8-5.3mm]
8382-XPG-522	.245 GROMMET I.D. FOR CABLE OD .22-.25 [5.6-6.4mm]
8382-XPG-526	.265 GROMMET I.D. FOR CABLE OD .25-.27 [6.4-6.7mm]
8382-XPG-528	.280 GROMMET I.D. FOR CABLE OD .265-.285 [6.7-7.2mm]


KIT P/N	NO. OF CONTACTS
8382-2PG-5XX	(2)-#16
8382-3PG-5XX	(3)-#16
8382-4PG-5XX	(4)-#16
8382-5PG-5XX	(5)-#16

GROMMET SIZE


NO. OF CONTACT




FACE VIEW
8382-2PG-5XX





FACE VIEW
8382-3PG-5XX



FACE VIEW
8382-4PG-5XX



FACE VIEW
8382-5PG-5XX



SHOWN ASSEMBLED KIT
FOR CUSTOMER REFERENCE ONLY

DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS

CUSTOMER APPROVAL			
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.			
APPROVED BY: _____			
DATE: _____			

RoHS COMPLIANT

B	MA	02-22-21	UPDATED MANUFACTURING DRAWING PER ECR 9544	
A	AN	04-09-19	DRAWING CREATED PER DOR 19-E149SL #5	
REV.	INIT.	DATE	DESCRIPTION	
AN		04-09-19	ORIG. DRAWN BY: AN	 601 E. WILDWOOD VILLA PARK, IL 60181
			CHECKED BY:	
			APPROVED BY:	
			SCALE: NTS, SIZE: B, SHEET: 1 OF 1	
			FILE: 8382-XPG-5XX, DIRECTORY: SLW	TITLE: CABLE TO CABLE CONN. ASS'Y (2-5) #16 PIN, SOLDER, LONG BACKSHELL MINI-CON-X
			CUSTOMER: STANDARD PRODUCT	
			PART NUMBER: 8382-XPG-5XX	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[8382-2PG-513](#) [8382-2PG-516](#) [8382-2PG-519](#) [8382-2PG-522](#) [8382-2PG-5XX](#) [8382-3PG-513](#) [8382-3PG-516](#)
[8382-3PG-519](#) [8382-3PG-522](#) [8382-3PG-5XX](#) [8382-4PG-513](#) [8382-4PG-516](#) [8382-4PG-519](#) [8382-4PG-522](#) [8382-](#)
[4PG-5XX](#) [8382-5PG-513](#) [8382-5PG-516](#) [8382-5PG-519](#) [8382-5PG-522](#) [8382-5PG-5XX](#)