


Detailed Specifications & Technical Data

BELDEN
SENDING ALL THE RIGHT SIGNALS

ENGLISH MEASUREMENT VERSION

AX106659 Faceplates and Panels - Angular MediaFlex Faceplate Kit for MDVO Modules, Single-gang



For more Information
please call

1-800-Belden1

General Description:

Angular MediaFlex MDVO Single-Gang Faceplate Kit 2-Port, Flush

Usage (Overall)

Suitable Applications: - Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400 and 1200.

Related Parts: - Compatible with 10GX, CAT6+ and CAT5E KeyConnect Modular Jacks and KeyConnect Multimedia Modules

Physical Characteristics (Connectivity)

Capacity

Max. Capacity: 2 ports

Access

Front Connection: Flush

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
4.500	2.750	0.455

Materials

Materials:

Description	Material
Faceplate	High-impact Thermoplastic, flame-retardant UL94V-0, UV-resistant
Insert	High-impact Thermoplastic, flame-retardant UL94V-0, UV-resistant

Color

Color: Elec. White

Weight

Weight: 0.103 lbs.

Included Parts

Included Parts: windows, papers, 6-32 screws, 2-ports inserts, 2U blank inserts, blank, installation guide

Packaging

Packaging: Individually packaged in a suitable plastic bag

Mechanical Characteristics (Connectivity)

Footprint/Type: KeyConnect

Connector/Hardware Retention: 20 lbs.

Storage Temperature Range: -40°C To +70°C

Installation Temperature Range: -10°C To +60°C

Operating Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2013

MII Order #39 (China RoHS): EUP 50

Suitability

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

AX106659 Faceplates and Panels - Angular MediaFlex Faceplate Kit for MDVO Modules, Single-gang

Suitability - Indoor:

Yes

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For proper installation refer to Installation Guide PX106224 included with the product or visit our web site at <http://www.belden.com>

Product Family

Part Numbers:

Description	Gray	Almond	Elec White	Black
Angular MediaFlex MDVO Single-Gang Faceplate Kit 2-Port, Flush	AX106657	AX106658	AX106659	AX106660
Angular MediaFlex MDVO Single-Gang Faceplate Kit 4-Port, Flush	AX106661	AX106662	AX106663	AX106664
Angular MediaFlex MDVO Single-Gang Faceplate Kit 6-Port, Flush	AX106665	AX106666	AX106667	AX106668

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX106659	1 EA	0.000 KG			MDVO ANG MFLEX KIT 2P ELW

Revision Number: 0 Revision Date: 10-14-2015

© 2016 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.